



Soldering Iron Tips

Our Paragon[®] Soldering Iron Tips Outlast Oridinary Tips Many Times Over.

A selection of Paragon[®] Soldering Iron Tips are available for all American Beauty[®] Irons! Available in a variety of sizes and shapes (Chisel, Conical, Diamond, Screwdriver, etc.) that fit American Beauty[®] Soldering Irons, as well as soldering irons from other manufacturers that accept plug-type tips.

Paragon®Tips define quality because of their:

- o Solid Copper Core
- o Iron Cladding
- Nickel Plating
- o Chrome Coating
- Pre-Tinned Tip
- o Plug-Type



Paragon Soldering Iron Tips Model 501

Specifications:

- Chisel Style
- Tip Diameter 1/8"(3.18mm)

- Shank Diameter 1/8" (3.18mm)
- Length 2 ¼" (57.15mm)

Used with the following tool:

• 3108 - Little Dandy Pencil-Style Soldering Iron



Paragon Soldering Iron Tips Model 502

Specifications:

- Chisel Style, Long TaperTip Diameter 1/8" (3.18mm)
- Shank Diameter 1/8" (3.18mm)
- Length 2 ¼" (57.15mm)

Used with the following tool:

• 3108 - Little Dandy Pencil-Style Soldering Iron


Iron Tips Model 830

Specifications:

- Screwdriver Style with Curved Ridge Catch
- Tip Diameter 1/4" (6.35mm)
- Shank Diameter 3/8" (9.53mm)
- Length 4 3/8" (111.1mm)

Used with the following tool:

• 3138 - Heavy-Duty Soldering Iron




Paragon Soldering Iron Tips Model 44D

Specifications:

- Diamond Style
- Shank Diameter 5/8" (15.88mm)
- Length 4 11/16" (118.87mm)

Used with the following tool:

• 3158 - Heavy-Duty Soldering Iron




Paragon Soldering Iron Tips Model 44C

Specifications:

- Chisel Style
- Tip Diameter 5/8" (15.88mm)
- Shank Diameter 5/8" (15.88mm)
- Length 4 11/16" (118.87mm)

Used with the following tool:

• 3158 - Heavy-Duty Soldering Iron



Paragon Soldering Iron Tips Model 45C

Specifications:

- Chisel Style
- Tip Diameter 7/8" (22.23mm)

- Shank Diameter 7/8" (22.23mm)
- Length 5 5/32" (130.90mm)

Used with the following tool:

• 3178 - Heavy-Duty Soldering Iron



Paragon Soldering Iron Tips Model 45D

Specifications:

- Diamond Style
- Shank Diameter 7/8" (22.23mm)
- Length 5 5/32" (130.90mm)

Used with the following tool:

• 3178 - Heavy-Duty Soldering Iron



Iron Tips Model 46C

Specifications:

- Chisel Style
- Tip Diameter 1 1/8" (28.58mm)
- Shank Diameter 1 1/8" (28.58mm)
- Length 5 7/8" (149.23mm)

Used with the following tool:

• 3198 - Heavy-Duty Soldering Iron



Paragon Soldering Iron Tips Model 46D

Specifications:

- Diamond Style
- Shank Diameter 1 1/8" (28.58mm)
- Length 5 7/8" (149.23mm)

Used with the following tool:

• 3198 - Heavy-Duty Soldering Iron

American Beauty Soldering Tools are proudly manufactured by Assembly Technologies International, Inc. 1177 West Maple Road Clawson, MI 48017-1059 United States (800) 550-2510 (248) 280-2810

Fax: (248) 280-2810

info@assemblytech.com