Shielded Cat. 5E Low Smoke Zero Halogen Cable, RJ45 M-M, 7.0 ft


Features for this product

- Low Smoke Zero Halogen (LSZH) Jacket for shipboard and aircraft usage
- Aluminized Polyester Shield for protection from EMI
- Low toxicity and non-corrosive jacket to protect equipment and people
- Category 5E rated for High Speed Network Performance
- Stock lengths up to 300 ft for direct runs to equipment




Designed for environments where PVC's combustive toxicity is restricted, L-com's Shielded Low Smoke Zero Halogen (LSZH) Ethernet Cables provide the ideal alternative. Featuring all-metal-body RJ45 connectors and aluminized Polyester shielded cable with drain wire, these assemblies are designed to protect from EMI/RFI while maintaining high performance data transmission characteristics. Ensure the protection of your investment by utilizing these L-com exclusive LSZH cables. Custom lengths and quantity pricing available. Talk to us about your project today!


Details for this Modular product	
L-com Item #	TRD855SZ-7
Manufacturer	L-com
UPC #	822335038394
RoHS Status	<u>RoHS Compliant 🥝</u>
Color	Black



SHIELDED CATEGORY 5E • 4 pair 26AWG stranded • LSZH jacket • Foil shielding





Modular > Category 5E Shielded LSZH Patch Cords 10



Category 5E Double Shielded Low Smoke Zero Halogen Patch Cables for High EMI/RFI Environments

When a single shield is not enough, L-com's exclusive double-shielded patch cables are ideal. EMI/RFI interference is drastically reduced due to L-com's superior cable shielding, a combination of a 100% foil plus a 60% braid shield. The Low Smoke Zero Halogen (LSZH) jacket allows this industrial patch cable to meet today's environmental and safety requirements.





Category 5E Double Shielded LSZH 26AWG Stranded Patch Cables



This series features 26AWG stranded conductors that are flexible and easy to install even in tight spaces. L-com stocks lengths up to 300 ft and can



DOUBLE SHIELDED CATEGORY 5E

- Double shielded foil+braid reduces EMI/RFI interference
- Low smoke zero halogen jacket for environmental and safety concerns
- 26AWG conductors for flexibility
- Stock lengths are available up to 300 ft.



ship most orders the same day.

TRD855 TRD855

TRD855

TRD855 TRD85

TRD85

TRD85

TRD855 TRD85

TRD855

TRD855

iray
iray
Gray
iray
Gray
Gray
iray
Gray
iray
iray

Category 5E Double Shielded LSZH 24AWG Solid Patch Cables

This series features 24AWG solid conductors allowing easy termination to IDC connectors. L-com stocks lengths up to 300 ft and can ship most orders the same day.

TRD855SIG-1	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 1.0 ft	Lt. Gray
TRD855SIG-2	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 2.0 ft	Lt. Gray
TRD855SIG-3	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 3.0 ft	Lt. Gray
TRD855SIG-5	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 5.0 ft	Lt. Gray
TRD855SIG-7	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 7.0 ft	Lt. Gray
TRD855SIG-10	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 10.0 ft	Lt. Gray
TRD855SIG-15	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 15.0 ft	Lt. Gray
TRD855SIG-25	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 25.0 ft	Lt. Gray
TRD855SIG-50	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 50.0 ft	Lt. Gray
TRD855SIG-75	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 75.0 ft	Lt. Gray
TRD855SIG-100	Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 100.0 ft	Lt. Gray