Industrial Grade Category 5E Dbl Shielded LSZH Patch Cord, 100.0 ft


Features for this product

- Category 5E Double Shielded RJ45 LSZH Patch Cables for Industrial Environments
- Foil plus Braid Shielding for maximum EMI/RFI protection
- 24AWG Solid conductors for termination to IDC blocks where required
- Exceeds EIA568 Category 5E requirements for high speed networks
- Stock lengths up to 300 ft for direct runs to equipment




For maximum protection against EMI/RFI interference, L-com's Double Shielded Patch cables are the right choice. With two layers of shielding (Foil plus Braid), data is protected from stray EMI/RFI fields. This series features 24AWG solid conductors allowing easy termination to IDC connectors. The rugged LSZH jacket is extra durable for harsh industrial environments. L-com stocks lengths up to 300 ft and can ship most orders the same day.

| Details for this Modular product | |
|----------------------------------|------------------|
| L-com Item # | TRD855SIG-100 |
| Manufacturer | L-com |
| UPC # | 822335037984 |
| RoHS Status | RoHS Compliant 🧭 |
| Color | Lt.Gray |




DOUBLE SHIELDED CATEGORY 5E • 4 pair 24AWG solid

- PVC jacket
- Foil + braid shielding





Modular > Category 5E Shielded LSZH Patch Cords 10



Category 5E Double Shielded Low Smoke Zero Halogen Patch Cables for High EMI/RFI Environments

When a single shield is not enough, L-com's exclusive double-shielded patch cables are ideal. EMI/RFI interference is drastically reduced due to L-com's superior cable shielding, a combination of a 100% foil plus a 60% braid shield. The Low Smoke Zero Halogen (LSZH) jacket allows this industrial patch cable to meet today's environmental and safety requirements.





Category 5E Double Shielded LSZH 26AWG Stranded Patch Cables



This series features 26AWG stranded conductors that are flexible and easy to install even in tight spaces. L-com stocks lengths up to 300 ft and can



DOUBLE SHIELDED CATEGORY 5E

- Double shielded foil+braid reduces EMI/RFI interference
- Low smoke zero halogen jacket for environmental and safety concerns
- 26AWG conductors for flexibility
- Stock lengths are available up to 300 ft.



ship most orders the same day.

TRD855 TRD855

TRD855

TRD855 TRD85

TRD85

TRD85

TRD855 TRD85

TRD855

TRD855

| iray |
|------|
| iray |
| Gray |
| iray |
| Gray |
| Gray |
| iray |
| Gray |
| iray |
| iray |
| |

Category 5E Double Shielded LSZH 24AWG Solid Patch Cables

This series features 24AWG solid conductors allowing easy termination to IDC connectors. L-com stocks lengths up to 300 ft and can ship most orders the same day.

| TRD855SIG-1 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 1.0 ft | Lt. Gray |
|---------------|---|----------|
| TRD855SIG-2 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 2.0 ft | Lt. Gray |
| TRD855SIG-3 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 3.0 ft | Lt. Gray |
| TRD855SIG-5 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 5.0 ft | Lt. Gray |
| TRD855SIG-7 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 7.0 ft | Lt. Gray |
| TRD855SIG-10 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 10.0 ft | Lt. Gray |
| TRD855SIG-15 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 15.0 ft | Lt. Gray |
| TRD855SIG-25 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 25.0 ft | Lt. Gray |
| TRD855SIG-50 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 50.0 ft | Lt. Gray |
| TRD855SIG-75 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 75.0 ft | Lt. Gray |
| TRD855SIG-100 | Double Shielded Cat. 5E LSZH Patch Cable, RJ45 / RJ45, 100.0 ft | Lt. Gray |