Shielded Cat. 5E EI A568 Patch Cable, RJ45 / RJ45, 3.0 ft

Features for this product


- Category 5E rated for High Speed Network Performance
- Aluminized Polyester Shield for protection from EMI
- EIA568 Compliant for compatibility with your network
- 26AWG stranded conductors for flexibility
- Available in lengths from 2 Ft to 100 Ft






For Protection against EMI/RFI interference L-com's economical Shielded Patch Cables are ideal. With a 100% foil shield covering 4-Pair 26AWG stranded conductors, your data is protected from interference. This series is designed to perform to EIA568 standards while not putting a strain on your budget. Quantity pricing available upon request.

| Details for this Modular product | | | | | |
|----------------------------------|------------------|--|--|--|--|
| L-com Item # | TRD855SCR-3 | | | | |
| Manufacturer | L-com | | | | |
| UPC # | 822335037922 | | | | |
| RoHS Status | RoHS Compliant 📀 | | | | |
| Color | Lt.Gray | | | | |




SHIELDED CAT. 5


- 4 pair 24AWG stranded
- PVC jacket
- Foil shielding




Screened (Shielded) Patch Cords










Item # Description Color

Shielded Category 5E Patch Cords with RJ45 (8x8) and RJ11 (6x4) Connectors

These screened (shielded) patch cords are great for a variety of electrically noisy environments where EMI is an issue. They utilize two or four pair cabling covered by a foil or foil+braid shield. Now available in flexible PVC, plenum and Low Smoke Zero Halogen jacket formulations. Assemblies are 100% tested and individually bagged.



✓ Category 5E Shielded RJ11 to RJ11 Patch Cords - 2 Pair USOC Wiring

| TRDU45SCR-2 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 2.0 ft | Beige |
|---------------|------------------------------------------------------------|-------|
| TRDU45SCR-3 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 3.0 ft | Beige |
| TRDU45SCR-5 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 5.0 ft | Beige |
| TRDU45SCR-7 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 7.0 ft | Beige |
| TRDU45SCR-10 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 10.0 ft | Beige |
| TRDU45SCR-15 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 15.0 ft | Beige |
| TRDU45SCR-25 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 25.0 ft | Beige |
| TRDU45SCR-50 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 50.0 ft | Beige |
| TRDU45SCR-100 | Shielded Cat. 5E USOC-4 Patch Cable, RJ11 / RJ11, 100.0 ft | Beige |
| | Turisted Dair Display, O.S. E. O.S. 4 | |

Twisted Pair Pinning: 2 & 5, 3 & 4.

Category 5E Shielded RJ45 to RJ45 Patch Cords - 4 Pair For EIA568A and B Wiring

| TRD855SCR-1 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 1.0 ft | lvory |
|---------------|------------------------------------------------------------|-------|
| TRD855SCR-2 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 2.0 ft | lvory |
| TRD855SCR-3 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 3.0 ft | lvory |
| TRD855SCR-5 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 5.0 ft | lvory |
| TRD855SCR-7 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 7.0 ft | lvory |
| TRD855SCR-10 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 10.0 ft | lvory |
| TRD855SCR-15 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 15.0 ft | lvory |
| TRD855SCR-20 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 20.0 ft | lvory |
| TRD855SCR-25 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 25.0 ft | lvory |
| TRD855SCR-30 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 30.0 ft | lvory |
| TRD855SCR-40 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 40.0 ft | lvory |
| TRD855SCR-50 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 50.0 ft | lvory |
| TRD855SCR-75 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 75.0 ft | lvory |
| TRD855SCR-100 | Shielded Cat. 5E EIA568 Patch Cable, RJ45 / RJ45, 100.0 ft | lvory |
| | Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8. | |

Category 5E RJ45 to RJ45 Shielded Plenum Patch Cords - 4 Pair Solid for EIA568A & B Wiring

| TRD855SPL-1 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 1.0 ft | Blue |
|---------------|------------------------------------------------------|------|
| TRD855SPL-2 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 2.0 ft | Blue |
| TRD855SPL-3 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 3.0 ft | Blue |
| TRD855SPL-5 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 5.0 ft | Blue |
| TRD855SPL-7 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 7.0 ft | Blue |
| TRD855SPL-10 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 10.0 ft | Blue |
| TRD855SPL-15 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 15.0 ft | Blue |
| TRD855SPL-25 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 25.0 ft | Blue |
| TRD855SPL-50 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 50.0 ft | Blue |
| TRD855SPL-75 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 75.0 ft | Blue |
| TRD855SPL-100 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 100.0 ft | Blue |
| TRD855SPL-150 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 150.0 ft | Blue |
| TRD855SPL-200 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 200.0 ft | Blue |
| TRD855SPL-250 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 250.0 ft | Blue |
| TRD855SPL-300 | Shielded Cat. 5E Plenum Cable, RJ45 / RJ45, 300.0 ft | Blue |
| | Twisted Pair Pinning: 1 & 2, 3 & 6, 4 & 5, 7 & 8. | |

Category 5E RJ45 to RJ45 Crossover Patch Cords

| Cutogory | of the to the to crossover that of the | |
|---------------|------------------------------------------------|----------|
| TRD855XCR-2 | Cat. 5E Crossover Cable, RJ45 / RJ45, 2.0 ft | Lt. Gray |
| TRD855XCR-3 | Cat. 5E Crossover Cable, RJ45 / RJ45, 3.0 ft | Lt. Gray |
| TRD855XCR-5 | Cat. 5E Crossover Cable, RJ45 / RJ45, 5.0 ft | Lt. Gray |
| TRD855XCR-7 | Cat. 5E Crossover Cable, RJ45 / RJ45, 7.0 ft | Lt. Gray |
| TRD855XCR-10 | Cat. 5E Crossover Cable, RJ45 / RJ45, 10.0 ft | Lt. Gray |
| TRD855XCR-15 | Cat. 5E Crossover Cable, RJ45 / RJ45, 15.0 ft | Lt. Gray |
| TRD855XCR-25 | Cat. 5E Crossover Cable, RJ45 / RJ45, 25.0 ft | Lt. Gray |
| TRD855XCR-50 | Cat. 5E Crossover Cable, RJ45 / RJ45, 50.0 ft | Lt. Gray |
| TRD855XCR-75 | Cat. 5E Crossover Cable, RJ45 / RJ45, 75.0 ft | Lt. Gray |
| TRD855XCR-100 | Cat. 5E Crossover Cable, RJ45 / RJ45, 100.0 ft | Lt. Gray |

1 & 2, 3 & 6 Crossover allows Ethernet Hub Stacking.