


# BUMPERS & GROMMETS


## Bumpers-Recessed



Part No.	A	B	C	D	E	F	Fig. No.
RCB-2062	3/8	1/4	3/16	1/16	1/4	5/32	1
RCB-2082S	5/8	1/2	1/4	1/4	5/16	5/32	1
RCB-2090S	5/8	5/8	7/16	3/16	5/16	.147	1
RCB-2184S	3/4	1/4	3/16	1/16	13/32	1/8	1
RCB-2084S	3/4	3/8	3/16	3/16	7/16	3/16	1
RCB-2096S	15/16	5/8	7/16	3/16	7/16	7/32	1
RCB-206	3/8	3/16	3/32	3/32	3/16	5/64	2
RCB-2061	7/16	5/32	3/32	1/16	1/4	5/32	2
RCB-207S	1/2	1/4	1/8	1/8	1/4	1/8	2
RCB-2081S	5/8	5/16	3/16	1/8	1/4	3/16	2
RCB-2088	5/8	5/16	3/16	1/8	1/4	1/8	2
RCB-2085S	3/4	3/8	3/16	3/16	5/16	5/32	2
RCB-209S	13/16	1/2	1/4	1/4	5/16	5/32	2
RCB-2097S	1	1	5/8	3/8	5/16	5/32	2
RCB-2099S	1	1-1/2	5/8	7/8	5/16	5/32	2
RCB-2095S	15/16	3/8	3/16	3/16	3/8	5/32	3
RCB-2197S	1	1/2	1/4	1/4	3/8	3/16	3

S = Steel washer molded into rubber.  
 Contains natural, synthetic or reclaimed rubber. Nominal durometer: 70.  
 1) Standard color is black (other colors available) 2) Ideal for cabinets, appliances, doors and windows 3) Other compounds available 4) Available in vinyl (see VRCB series).


## Bumpers-Machine Screw (Male & Female)



Part No.	A	B	C	Screw Size
MCH-51	1/2	1/4	1/4	8-32
MCH-62	5/8	5/16	1/4	8-32
MCH-75	3/4	3/8	1/4	8-32
MCH-100	1	1/2	1/2	10-32
FMCH-868-2	5/8	5/16	1/4	8-32

Nominal durometer: 75. Ideal for vibration dampening or under heavy appliances. Larger sizes available.


## Bumpers-Button



Part No.	A	B	C	D	E	F	Fig. No.
BTN-4061	3/8	5/16	3/16	1/4	1/8	1/16	1
BTN-4161	3/8	11/32	3/16	1/4	1/8	3/32	1
BTN-3072	1/2	21/64	9/32	3/8	1/8	3/64	1
BTN-4171	1/2	7/16	3/16	1/4	3/16	1/16	1
BTN-407	1/2	7/16	1/4	11/32	1/4	1/16	2
BTN-308	5/8	9/16	3/8	15/32	5/16	.040	2
BTN-3263	7/16	7/16	1/4	5/16	3/16	1/8	3

Nominal durometer: 55-65. Many other sizes and compounds available. Available in vinyl (see VBTN series).

## Bumpers-Stern



Part No.	A	B	C	D	E
STM-6011W	1/4	5/16	1/8	3/16	1/8

W = WHITE  
 Nominal durometer: 65. Available in vinyl (see VSTM series).

Contents of all molded products are blends or combinations of natural, synthetic or reclaimed rubber. Items are listed by diameter and height in ascending order.