


3 VOLT LITHIUM COIN CELLS




PART NO.	X-REF	VOLTS	mAh	Dia. x Hgt. (MM)
LITH-26	BR1216	3	25	12 x 1.6
LITH-2	BR1225	3	40	12 x 2.5
LITH-47	BR1616	3	48	16 x 1.6
LITH-44	BR1632	3	120	16 x 3.2
LITH-4	BR2016	3	75	20 x 1.6
LITH-27	BR2020	3	100	20 x 2.0
COMP-141	BR2032	3	190	20 x 3.2
LITH-5	BR2320	3	110	23 x 2.0
COMP-2	BR2325	3	175	23 x 2.5
COMP-60	BR2330	3	255	23 x 3.0
LITH-38	BR2335	3	165	23 x 3.5
LITH-45	BR3032	3	500	30 x 3.2
LITH-25	CR1025	3	30	10 x 2.5
LITH-31	CR1216	3	25	12 x 1.6
LITH-1	CR1220	3	35	12 x 2.0
LITH-52	CR1225	3	50	12 x 2.5

PART NO.	X-REF	VOLTS	mAh	Dia. x Hgt. (MM)
LITH-20	CR1616	3	50	16 x 1.6
LITH-3	CR1620	3	60	16 x 2.0
LITH-34	CR1632	3	120	16 x 3.2
LITH-24	CR2012	3	55	20 X 1.2
COMP-30	CR2016	3	75	20 x 1.6
COMP-31	CR2025	3	150	20 x 2.5
COMP-32	CR2032	3	200	20 x 3.2
LITH-23	CR2040	3	280	20 x 4.0
LITH-30	CR2320	3	120	23 x 2.0
COMP-101	CR2330	3	265	23 x 3.0
COMP-61	CR2354	3	560	23 x 5.4
COMP-1	CR2430	3	270	24 x 3.0
¹ COMP-33	CR2450	3	550	24 x 5.0
² COMP-33R RENATA	CR2450R	3	550	24 x 5.0
³ COMP-33 SANYO	CR2450	3	550	24 x 5.0
LITH-32	CR2477	3	950	24 x 7.7
LITH-33	CR3032	3	500	30 x 3.2

NOTE:
 1= NO RIDGE
 2= REVERSE POLARITY WITH RIDGE
 3= NORMAL POLARITY WITH RIDGE

3 VOLT LITHIUM COIN CELLS WITH SOLDER TABS

PART NO.	X-REF	VOLTS	mAh	DESCRIPTION
PLAIN SOLDER TAB FOR ATTACHING WIRE				
LITH-2-1	BR1225-T	3	40	SOLDER TAB
LITH-27-1	BR2020-T	3	100	SOLDER TAB
COMP-2-1	BR2325-T	3	175	SOLDER TAB
COMP-60-1	BR2330-T	3	255	SOLDER TAB
LITH-25-1	CR1025-T	3	30	SOLDER TAB
LITH-31-1	CR1216-T	3	25	SOLDER TAB
LITH-1-1	CR1220-T	3	35	SOLDER TAB
LITH-3-1	CR1620-T	3	60	SOLDER TAB
COMP-30-1	CR2016-T	3	75	SOLDER TAB
COMP-31-1	CR2025-T	3	150	SOLDER TAB
COMP-32-1	CR2032-T	3	200	SOLDER TAB
LITH-23-1	CR2040-T	3	280	SOLDER TAB
LITH-30-1	CR2320-T	3	130	SOLDER TAB
COMP-61-1	CR2354-T	3	560	SOLDER TAB
COMP-1-1	CR2430-T	3	270	SOLDER TAB
COMP-33-1	CR2450-T	3	550	SOLDER TAB



SOLDER TABS