

DANTONA

INDUSTRIES, INC.

For all your battery needs!



YUASA
Lead Acid
Batteries


DANTONA PART SEARCH



Dantona Part # LAP-180
SMART


Voltage: 10.8
Capacity: 4000
Composition: NIMH
Dimensions:
Connector:

LAPTOP/NOTEBOOK COMPUTER PACKS



Part No.	Pic. #	Volts	Cap.	Size - Inches (L x W x H)	Termination
LAP-150	1	14.4	1500	7.125 x 2.125 x .75	4 Contacts on Same Side
LAP-151	2	7.2	2400	5.9375 x 2.625 x .6875	3 Contacts on Same Side
LAP-152	5	12	1700	6.8125 x 2.6875 x .75	3 Contacts on End
LAP-153	6	14.4	1700	5.5 x 4.5	5 Contacts on End
LAP-154	7	14.4	1700	5.5 x 4.5 x .875	5 Contacts on End
LAP-155	8	7.2	1400	5.75 x 2.125 x .5	3 Pin Connector
LAP-156	9	12	1800	9.75 x 1.25 x .625	3 Contacts on Top
LAP-157	10	9.6	3300	5.25 x 4.125 x .75	7 Contacts on End
LAP-158				CONTACT FACTORY	
LAP-159	11	14.4	1700	6.875 x 3.5 x .875	5 Contacts on End
LAP-160D	3	12	2500	5.5 x 3.625 x .75	3 Contacts on Same Side
LAP-160L	3	12	2500	5.5 x 3.625 x .75	3 Contacts on Same Side
LAP-161	12	12	2800	9.5 x 2 x 1	2 Contacts on End
LAP-162	13	9.6	2300	4.125 x 3.625 x 1	3 Contacts on End
LAP-163	15	7.2	3400	4.6875 x 4.5 x .75	4 Contacts on End

Part No.	Pic. #	Volts	Cap.	Size - Inches (L x W x H)	Termination
LAP-163SM	15	7.2	2800	6.75 x 3 x .75	5 Contacts on Same Side
LAP-164	16	7.2	2800	4.5 x 4.25 x .75	3 Contacts on End
LAP-165	17	12	2500	6.75 x 3 x .75	5 Contacts on Same Side
LAP-166	23	6	4000	5.5 x 4.25 x .75	4 Contacts on Top
LAP-166NMH	23	6	4000	5.5 x 4.25 x .75	4 Contacts on Top
LAP-167	18	12	1700	5.5 x 3.5 x .8125	3 Contacts on Same Side
LAP-168	19	12	1400	10 x 1.25 x .6875	2 Contacts on End
LAP-169	4	6	4000	5.5 x 4.25 x .75	4 Contacts on Top
LAP-169NMH	4	6	4000	5.5 x 4.25 x .75	4 Contacts on Top
LAP-170	14	12	2500	5.5 x 3.6875 x 2.15625	3 Contacts on End
LAP-171	20	14.4	1700	7.875 x 2.625 x .6875	3 Contacts on End
LAP-171NMH	20	14.4	1700	7.875 x 2.625 x .6875	3 Contacts on End
LAP-172	21	12	4200	4.625 x 3.625 x 2	2 Pin Connector
LAP-173	22	12	2400	11.8125 x 1.875 x 1	5 Contacts on Same Side
LAP-174	24	14.4	2400	5.5 x 4.5 x .8125	5 Contacts on End



Part No.	Pic. #	Volts	Cap.	Size - Inches (L x W x H)	Termination
LAP-175	1	9.6	2400	5.375 x 2.625 x .6875	3 Contacts on End
LAP-176	2	14.4	1700	10.5625 x 1.9375 x .625	2 Contacts on End
LAP-177	3	8.4	2400	4.875 x 3 x .75	3 Contacts on End
LAP-178	4	12	2800	10.25 x 2 x 1.125	3 Contacts on End
LAP-179	9	12	1800	4.125 x 3.8125 x .75	4 Contacts on End
LAP-180	6	10.8	3000	8.435 x 2 x .6875	5 Contacts on End
LAP-180SMART	6	10.8	3000	8.435 x 2 x .6875	5 Contacts on End
LAP-181	7	12	2800	5.5 x 3.375 x .6875	5 Contacts on Same Side
LAP-181SMART	7	12	2800	5.5 x 3.375 x .6875	5 Contacts on Same Side
LAP-182	8	12	2400	5.8125 x 3.5 x .90625	5 Contacts on End
LAP-182LI	8	12	2400	5.8125 x 3.5 x .90625	5 Contacts on End
LAP-183	11	9.6	1700	5.375 x 2.625 x .625	2 Contacts on End
LAP-184	12	12	1400	9.75 x .0625 x .625	3 Pin Connector
LAP-185	5	9.6	1800	4.25 x 3 x .75	4 Pin Connection on End
LAP-186				CONTACT FACTORY	
LAP-187	15	19.2	1700	5.6875 x 2.8125 x 1.3125	2 Contacts 1 Right Side, 1 Left Side

Part No.	Pic. #	Volts	Cap.	Size - Inches (L x W x H)	Termination
LAP-188	16	10.8	3600	6.75 x 2.75 x .6875	10 Contacts on End 2 on Bottom
LAP-189	17	10.8	3000	5.625 x 2 x .6875	5 Contacts on End
LAP-190	18	8.4	3500	4.5 x 4 x .75	7 Contacts on End
LAP-191	13	9.6	3000	4.5 x 2.125 x .75	3 Contacts on End
LAP-192	19	7.2	7000	4.25 x 4.25 x .75	3 Contacts on End
LAP-193	10	8.4	2500	4.25 x 2.75 x 1.0625	3 Contacts on Same Side
LAP-194	21	12	3400	5.9375 x 3.875 x .75	5 Contacts on End
LAP-195	22	12	1800	3.625 x 3.5 x .75	4 Contacts on End
LAP-196	23	12	3000	6.75 x 2.875 x .75	3 Contacts on Top
LAP-197	14	9.6	3000	4.125 x 4.125 x .75	6 Contacts on End
LAP-198	16	10.8	3500	6.75 x 7.75 x .6875	10 Contacts on End 2 on Bottom
LAP-199	20	16.8	1800	4.5 x 4.125 x .75	5 Contacts on End
LAP-199LI	20	16.8	1800	4.5 x 4.125 x .75	5 Contacts on End