

DANTONA

INDUSTRIES, INC.

For all your battery needs!

Lead Acid Batteries



DANTONA PART SEARCH



Dantona Part # LAP-358LI

Voltage: 11.1
Capacity: 3600
Composition: LION
Dimensions: 9.0" X 2.40" X .55"
Connector:

DANTONA

INDUSTRIES, INC.




For all your battery needs!

Power Tool Replacement Batteries



DANTONA CATALOG

DELL

	Part #	Volts	mAh	Type	X-Ref	
	6-1/3AASK-U	7.2	110	NiCd	DELL: 212N, 320N, 42873	
	COMP-10	** NO **	** LONGER **	** AVAILABLE **	DELL: 286AT, 300, 310, 316, 325, 386, SYSTEM 200	
	COMP-9	7.2	1900	Lithium	DELL: SYSTEM 200/286	

	LAP-327LI	14.4	5400	LION	DELL: 2941E, 6171R, 9943E, F1540A, INSPIRON 7000, INSPIRON 7500
	LAP-346LI	14.8	4000	LION	DELL: 1G222, 1N187, 2G218, 2G248, 2N135, 312-0022, 312- 0058, 7F948, 8F867, 8F871, BAT3151L8, BAT315LBA, BATACTY13L8, INSPIRON 2650, INSPIRON 2650/C
	LAP-358LI	11.1	3600	LION	DELL: 01J989, 1J989, 312-0025, 312-4609, LATITUDE C400
	LAP-363-111-78	11.1	7800	LION	DELL: 312-0427, 312- 0428, 312-0460, 312- 0461, 312-0466, 312- 0467, 312-0599, 312- 0600, 451-10338, 451- 10339, 451-10424, 451-10482, GD761, INSPIRON 1501, INSPIRON 6400, INSPIRON E1505, KD476, LATITUDE 131L, PD942, PD945, PD946, PR002, RD850, RD855, RD857, RD859, TD344, TD347, TD349, UD260, UD264, UD265, UD267, VOSTRO 1000, XU937
	LAP-363LI-111	11.1	4400	LION	DELL: 312-0427, 312- 0428, 312-0460, 312- 0461, 312-0466, 312- 0467, 312-0599, 312- 0600, E1501, E1505, INSPIRON 6400, KD476, LATITUDE 131L, TD344, TD347, TD349, UD260, UD264, UD265, VOSTRO 1000
	LAP-363LI-148	14.8	2000	LION	DELL: E1501, E1505, INSPIRON 6400, LATITUDE 131L, UD267