


# Steel Storage Cabinets



Steel cabinets stack together for high-density storage.

- Store, consolidate, and organize small parts.
- Two cabinets fit side by side on standard 36" wide shelving.
- Drawers are removable and are rust, corrosion, and dent-proof.
- No sharp edges to damage parts.
- Unique rear stop tab on each drawer prevents spills.
- Additional dividers, labels, and replacement drawers can be purchased separately.
- Color: Gray.



### 19-Series Heavy-Duty Cabinets

Cabinet frame: 17" wide x 11" deep x 11" high with 10<sup>9</sup>/<sub>16</sub>" drawer depth. Steel cabinets have five different drawer sizes. Each drawer includes two removable dividers and one label. Seven divider slots per drawer. Optional security cabinet with locking door.



### 17-Series Light-Duty Cabinets

Cabinet frames: 18" wide x 6" deep x 9<sup>1</sup>/<sub>2</sub>" high with 5<sup>3</sup>/<sub>4</sub>" drawer depth.



### Two Drawer Depths

#### 19-Series



#### 17-Series



17-Series have 5<sup>3</sup>/<sub>4</sub>" deep drawers. 19-Series have extra-deep 10<sup>9</sup>/<sub>16</sub>" drawers for optimum storage flexibility.

### Steel Storage Cabinets


Model No.	Description	Drawers Per Cabinet	Drawer Dimensions						Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
			Inches			mm					
			W	H	D	W	H	D			
<b>19-Series Heavy-Duty 17" W x 11" D x 11" H (432 x 279 x 279mm)</b>											
19228	Storage Cabinet*	28	2 <sup>3</sup> / <sub>16</sub>	2 <sup>1</sup> / <sub>16</sub>	10 <sup>9</sup> / <sub>16</sub>	56	52	268	1	20228 40228	
19320	Storage Cabinet*	20	3 <sup>3</sup> / <sub>16</sub>	2 <sup>1</sup> / <sub>16</sub>	10 <sup>9</sup> / <sub>16</sub>	81	52	268	1	20320 40320	
19416	Storage Cabinet*	16	4	2 <sup>1</sup> / <sub>16</sub>	10 <sup>9</sup> / <sub>16</sub>	102	54	268	1	20416 40416	
19715	Storage Cabinet*	15	3 <sup>3</sup> / <sub>16</sub>	3 <sup>1</sup> / <sub>16</sub>	10 <sup>9</sup> / <sub>16</sub>	81	78	268	1	20715 40715	
19909	Storage Cabinet*	9	5 <sup>3</sup> / <sub>16</sub>	3 <sup>1</sup> / <sub>16</sub>	10 <sup>9</sup> / <sub>16</sub>	132	78	268	1	20909 40909	
19109	Security Cabinet w/ locking door	9	5 <sup>3</sup> / <sub>16</sub>	3 <sup>1</sup> / <sub>16</sub>	10 <sup>9</sup> / <sub>16</sub>	132	78	268	1	20909 40909	
<b>17-Series Light-Duty 18" W x 6" D x 9<sup>1</sup>/<sub>2</sub>" H (457 x 152 x 241mm)</b>											
17018	Storage Cabinet	18	2 <sup>3</sup> / <sub>4</sub>	2 <sup>1</sup> / <sub>2</sub>	5 <sup>3</sup> / <sub>4</sub>	70	64	146	1	20902 40901	
17136	Storage Cabinet	36	2 <sup>3</sup> / <sub>4</sub>	1 <sup>1</sup> / <sub>4</sub>	5 <sup>3</sup> / <sub>4</sub>	70	32	146	1	20502 40501	

\*Available with a locking door when ordered in quantities of 50 or more.

# Storage Cabinet Hanging Systems

### Mobile Steel Cabinet Rack\*

Double-sided, mobile rail rack holds 12 of the 19-Series cabinets with as many as 336 drawers. Supports up to 500 lbs.



### Order These Components and Quantities

- 30012 Double-Sided Rail Rack – Qty: 1
- 30424 Mobile Kit – Qty: 1
- 19-Series Cabinets – Mix or Match – Qty: 12
- 98400 Suspension Straps (Set of 2 straps) – Qty: 12 Sets

\*Assembly required



### Storage-Go-Round\*

Access 20 cabinets and as many as 560 drawers in less than three square feet of floor space. Holds up to 1,000 lbs. of parts.

Accommodates Akro-Mils 19-Series Steel Cabinets (sold separately).

### Order These Components and Quantities

- 98325 Storage-Go-Round with turntable base
- Assembled Storage-Go-Round stands 31" L x 31" W x 60" H (787 x 787 x 1524 mm)

19-Series Cabinets – Mix or Match – Qty: 20

\*Assembly required

# Storage Cabinets



- Strong plastic cabinets organize and protect components.
- A variety of drawer configurations provide versatile storage solutions.
- Cabinets stack securely and are wall mountable.
- Dividers won't get lost - molded into cabinet back.



I.D. Size: 4<sup>3</sup>/<sub>8</sub>W x 2H x 5<sup>1</sup>/<sub>4</sub>L



I.D. Size: 2<sup>1</sup>/<sub>8</sub>W x 1<sup>1</sup>/<sub>2</sub>H x 5<sup>1</sup>/<sub>4</sub>L

Akro-Mils' clarified polypropylene drawers are the best in the industry!

- Unbreakable - no cracked drawers in shipping unlike polystyrene drawers
- Flexible, strong, and see-through
- Chemical-resistant



10116



10126



10144



10164


## Storage Cabinets

Model No.	Description	L	Inches			L	mm		Ctn. Qty.
			W	H		W	H		
10116	16-Drawer Cabinet	10 <sup>9</sup> / <sub>16</sub>	8 <sup>1</sup> / <sub>2</sub>	6 <sup>3</sup> / <sub>8</sub>	268	216	162	1	
10126	26-Drawer Cabinet	20	10 <sup>11</sup> / <sub>32</sub>	6 <sup>3</sup> / <sub>8</sub>	508	263	162	1	
10124	24-Drawer Cabinet	20	15 <sup>13</sup> / <sub>16</sub>	6 <sup>3</sup> / <sub>8</sub>	508	402	162	1	
10144	44-Drawer Cabinet	20	15 <sup>13</sup> / <sub>16</sub>	6 <sup>3</sup> / <sub>8</sub>	508	402	162	1	
10164	64-Drawer Cabinet	20	15 <sup>13</sup> / <sub>16</sub>	6 <sup>3</sup> / <sub>8</sub>	508	402	162	1	

16-Drawer Cabinet has 8 dividers. All other cabinets have 8 small and 4 large dividers.

# Tote Caddy

- Hand-held tool and supply caddy.
- Deep compartments hold loose parts, cleaning supplies, or tools for easy transport.
- Molded of heavy-duty, industrial-grade polypropylene for lasting durability.
- Color: Blue.



8" deep compartments are ideal for hardware, automotive items, or cleaning supplies

## Tote Caddy

Model No.	Description	Size		Ctn. Qty.
		Inches	mm	
09185	Tote Caddy	13 <sup>3</sup> / <sub>4</sub> x 18 <sup>1</sup> / <sub>4</sub> x 8 <sup>3</sup> / <sub>4</sub>	349 x 464 x 222	6


# Storage Cases

## Small Cases




0 Fixed Dividers  
4 Adjustable Dividers

## Medium Cases




1 Fixed Divider  
4 Adjustable Dividers

## Small & Medium Cases



2 Fixed Dividers  
4 Adjustable Dividers

## Large Cases



2 Fixed Dividers  
5 Adjustable Dividers

- Grid design in lid keeps items from spilling into other compartments.
- Cases available in 3 sizes with different divider configurations.
- Small and medium cases include 4 front-to-back adjustable dividers.
- Large cases include 5 front-to-back adjustable dividers.



05705  
Small Case

05905  
Large Case

05805  
Medium Case

## Storage Cases

Model No.	Description	Inches			mm			Maximum Compartments	Ctn. Qty.
		L	W	H	L	W	H		
05705	Small Case (2 Fixed Dividers)	8 <sup>5</sup> / <sub>8</sub>	5 <sup>1</sup> / <sub>8</sub>	1 <sup>5</sup> / <sub>8</sub>	219	130	41	15	12
05709	Small Case (0 Fixed Dividers)	8 <sup>5</sup> / <sub>8</sub>	5 <sup>1</sup> / <sub>8</sub>	1 <sup>5</sup> / <sub>8</sub>	219	130	41	5	12
05805	Medium Case (2 Fixed Dividers)	11	7	2 <sup>3</sup> / <sub>8</sub>	279	178	60	15	6
05807	Medium Case (1 Fixed Divider)	11	7	2 <sup>3</sup> / <sub>8</sub>	279	178	60	10	6
05905	Large Case (2 Fixed Dividers)	14 <sup>3</sup> / <sub>8</sub>	9 <sup>1</sup> / <sub>2</sub>	2 <sup>1</sup> / <sub>2</sub>	365	241	64	18	6

# Portable Organizers

- Unique design keeps parts and equipment from migrating to other compartments when lids are shut.
- Separate lid compartment holds small items.
- The main compartment holds larger, bulky items.
- Dividers included for both levels.
- Molded-in "feet" allow case to stand upright.



## Portable Organizers

Model No.	Description	No. of Compartments	Inches			mm			Ctn. Qty.
			L	W	H	L	W	H	
06115	Lid Storage Organizer	11 to 46 compartments	15	11 <sup>5</sup> / <sub>16</sub>	3 <sup>1</sup> / <sub>4</sub>	381	287	83	1
06118	Large Lid Storage Organizer	12 to 62 compartments	18 <sup>1</sup> / <sub>4</sub>	13 <sup>3</sup> / <sub>8</sub>	3 <sup>3</sup> / <sub>8</sub>	464	340	92	1
06217	Flat-Bottom Organizer	9 to 32 compartments	11 <sup>15</sup> / <sub>16</sub>	15	3 <sup>7</sup> / <sub>8</sub>	303	381	98	6



# Roto-Shelf

- Mobile storage unit can easily be moved to different work areas.
- Roto-Shelf is ideal for assembly components.
- 19<sup>7</sup>/<sub>8</sub>" wide unit takes up very little floor space.
- Four shelves rotate on an independent central metal shaft.

## Roto-Shelf

Model No.	Inches	mm		Ctn. Qty.	
		D	H		W
02420	19 <sup>7</sup> / <sub>8</sub>	37 <sup>1</sup> / <sub>2</sub>	502	953	1

Shelf depth - 2<sup>1</sup>/<sub>8</sub>" Shelf diameter - 19<sup>7</sup>/<sub>8</sub>" 75 lbs. per shelf  
300 lb. total wt. capacity

# Tilt & Locks

- Locking storage bins make this unit great in vehicles, mounted behind doors, or anywhere a convenient storage center is needed.
- Three sizes stack and lock together to form a customized storage center.

## Tilt & Locks

Model No.	Description	Inches			mm			Ctn. Qty.
		L	W	H	L	W	H	
08146	Small	19 <sup>5</sup> / <sub>8</sub>	2 <sup>3</sup> / <sub>4</sub>	5 <sup>1</sup> / <sub>4</sub>	498	70	133	1
08166	Medium	19 <sup>5</sup> / <sub>8</sub>	3 <sup>3</sup> / <sub>4</sub>	6 <sup>7</sup> / <sub>8</sub>	498	95	175	1
08186	Large	19 <sup>5</sup> / <sub>8</sub>	5 <sup>1</sup> / <sub>4</sub>	8 <sup>3</sup> / <sub>8</sub>	498	146	213	1