# GENERAL ACCESSORIES

## **Power Supplies & Spectrum Analyzers**

#### **Power Supply Accessory Kit**

**TLPS** 

The TLPS accessory kit combines safety and functionality. A must have for anyone who uses a power supply, this kit is ideal for use with power supplies in educational, service and maintenance, and manufacturing applications.

- High capacity silicone jacketed leads
- Connection adapters
- Medium and large insulated alligator clips
- Black and red components
- Sense lead included

Description	Qty.	(IEC Rating)	Voltage Current Max.
Retractile Leads, 120cm (48") (colors)	*2	600 V CAT II	25 A
6/4mm Spade Lug Adapters, (colors)	*2	33 Vdc/ 70 Vac	36 A
Standard Alligator Clips, (colors)	*2	300 V CAT I	3 A
4mm Banana Plug Adapters (colors)	*2	33 Vdc/ 70 Vac	36 A
Insulated Alligator Clips, (colors)	*3	600 V CAT IV	36 A
Sense Lead Pair, 1 m (Black & Red)	1	33 Vdc/ 70 Vac	3 A

<sup>\*</sup> Colors: Black & Red

### **General Purpose Universal Coaxial Adapter Kit**

CT2701A

The CT2701A provides a convenient solution for most interconnection needs. This adapter kit, with its 6 universal adapter, allows assembly of hundreds of different coaxial adapters: male to male, female to female, male to female, in-series and between-series for BNC, TNC, N-Type, F, RCA, SMA, UHF and Mini-UHF.

Description	Qty.
Universal Adapters	6
BNC male Adapters	2
BNC female Adapters	2
F male Adapter	1
F female Adapter	1
N Type male Adapters	2
N Type female Adapters	2
RCA male Adapter	1
RCA female Adapter	1
SMA male Adapter	1
SMA female Adapter	1
TNC male Adapters	2
TNC female Adapters	2
UHF male Adapters	2
UHF female Adapters	2
Mini-UHF male Adapter	1
Mini-UHF female Adapter	1



- Convenient interconnection kit
- BNC, TNC, N, SMA, RCA, F, SMA & Mini-UHF connectors
- Tarnish resistant nickel finish
- Gold plated center contacts
- Zippered storage case



#### **General Purpose Power Supply Accessory Kit**

CC 545

The CC 545 kit provides most everything needed to put a bench power supply to work.

- High capacity retractable sheath silicone jacketed leads
- Connection adapters
- Extra-large insulated alligator clips
- Black, red and green components
- Coaxial accessories for RF testing
- Storage case

Description	Qty.	(IEC Rating)	Voltage
<u> </u>	Ť		Current Max.
Retractile Lead, 100cm (40"), Black	*3	600 V CAT II	36 A
6/4mm Spade Lug Adapter, Black	*3	33 Vdc/ 70 Vac	36 A
BNC Cable Assembly, 100cm (40")	1	500 Vrms	3 A
BNC female to Double Banana Plugs	I	500 Vrms	3 A
Banana Plug Adapter, Black	*3	33 Vdc/ 70 Vac	36 A
BNC male to Double Binding Posts	1	500 Vrms	3 A
Insulated Alligator Clip, Black	*3	600 V CAT IV	36 A

<sup>\*</sup> Colors: Black, Red & Green

# **5A Banana Plug Power Supply Cables**TL 5A



Description	Qty.	IEC Rating	Voltage Current Max.
Leads, 4mm Banana Plug Leads, 100cm (40")	*2	33 Vdc/ 70 Vac	5 A

#### **30A Power Supply Cable**

TL 30

#10 Spade lug to large battery clip



Description	Qty.	IEC Rating	Voltage Current Max.
Cables, #10 Lug to Battery Clip, 75cm (30")	*2	33 Vdc/ 70 Vac	30 A