

ADAPTERS/COUPLERS



Surface Jack Modular Converter

Converts standard or "hardwired" installations to modular. Screw terminals for easy installation. Modular cover fastens to existing connecting block.

Ivory Cat. No. 30-9600-0000

(4-Prong) system.

Cat. No. 30-9650-0000

Cat. No. 30-9650-00BU

White Cat. No. 30-9601-0000 Complies with USOC number RJ11C

Standard to Modular Adapter Adapts modular plug ends to standard



Spade Lug to Modular Plug Adaptor

Converts "hardwire" telephone to modular system. Screw terminals for easy installation. **Cat. No. 30-9652-0000**

Modular T Adapter

"T" adapter enables two modular plugs to be used in a single modular jack.

4-Conductor Ivory Cat. No. 30-9654-0000 Cat. No. 30-9654-00BU

4-Conductor White Cat. No. 30-9615-0000 Cat. No. 30-9615-00BU

6-Conductor Ivory Cat. No. 30-9647-0000 Cat. No. 30-9647-00BU

6-Conductor White Cat. No. 30-9646-0000 Cat. No. 30-9646-00BU

8-Conductor Duplex Adapter

Converts one 8-conductor jack into two 8-conductor jacks for telephone or data interfaces.

8-Conductor Ivory Cat. No. 30-9649-0000 Cat. No. 30-9649-00BU

8-Conductor White Cat. No. 30-9648-0000 Cat. No. 30-9648-00BU

Modular Triplex Adapter

Allows three modular plugs to be used in a single modular jack.

Cat. No. 30-9656-0000 Cat. No. 30-9656-00BU





Two-Line Adapter

Converts a two-line system into two single line outlets. Cat. No. 30-9655-0000

Two-Line Triplex Adapter

Converts a single jack with 2-line service to a line 1 jack, line 2 jack and a combo line 1-2 jack. **Cat. No. 30-9658-0000**

Modular Three-Line Triplex Adapter

This adapter allows multiple equipment to share the same telephone line. It does provide additional dial tones or split a 3 line system into line1, line 2 and line 3, if your home or office is wired with a minimum 6 conductor installation wire. Works with all brands.

Ivory Cat. No. 30-9663-0000

White Cat. No. 30-9664-0000

2-Line Y-Coupler

Couples two single-line jacks into one 2line jack. For use with 2-line devices, with modular plug. 12 Ft. Ivory

Cat. No. 30-9505-0000

Modular In-line Couplers

Allows two modular line cords to be connected together to increase length.

Configuration	Description	Part No.
Reverse	4-Conductor Ivory	30-9678-0000 30-9678-00BU
Reverse	4-Conductor White	30-9618-0000 30-9618-00BU
Reverse	6-Conductor Ivory	30-9686-0000 30-9686-00BU
Reverse	6-Conductor White	30-9687-0000 30-9687-00BU
Reverse	8-Conductor Ivory	30-9688-0000 30-9688-00BU
Reverse	8-Conductor White	30-9689-0000 30-9689-00BU
Straight Thru	6-Conductor Ivory	30-9682-0000 30-9682-00BU
Straight Thru	6-Conductor White	30-9683-0000 30-9683-00BU
Straight Thru	8-Conductor Ivory	30-9684-0000 30-9684-00BU
Straight Thru	8-Conductor White	30-9685-0000 30-9685-00BU













Revise thing in the second sec

TELEPHONE 13