HellermannTyton

596-00499

WARNING

TURN OFF PHOTOVOLTAIC AC DISCONNECT PRIOR TO WORKING INSIDE PANEL

Article Number: 596-00499

Pre-Printed Solar Label, "WARNING - TURN OFF PV BEFORE WORKING...", 4.125" X 2", Vinyl, Orange/White, 50/RL

RoHS



Base Data

Local Order Number 596-00499

Type WTOPVLBL

Color Orange (OG)

- Features and Benefits Made with UV stable inks and materials for durability and weather resistance.
 - The labels are supplied with aggresive adhesive to ensure long life.
 - · Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Product Description HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptalbe to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Technical Description 4.12" X2" Black text on an Orange/White background that reads as: "WARNING - TURN OFF PHOTOVOLTAIC AC DISCONNECT PRIOR TO WORKING INSIDE PANEL." - 50 per roll.

Local Order Number 2 Spanish Version: 596-00806

Short Description Pre-Printed Solar Label, "WARNING - TURN OFF PV BEFORE WORKING...", 4.125" X2", Vinyl, Orange/White,

Product Dimensions

Length L (Imperial) 4.125 "

Length L (Metric) 104.6 mm

Width W (Imperial) 4.125 "

Width W (Metric) 104.6 mm

Height H (Imperial) 2.0 "

Height H (Metric) 50.8 mm

Logistics and Packaging

Quantity Per roll

Package Quantity

Package Quantity (Metric) 50

Labels per Column 1

Labels per Row 1

Material and Specifications

Material Type 443/552, UV Stable Flexible White Vinyl w/Acryclic Laminate

Material Shortcut 443/552

Adhesive Shortcut Acrylic

Adhesive Acrylic

Adhesive Operating Temperature -40°F to +174°F (-40°C to +79°C)

Halogenfree Yes

Operating Temperature $-40^{\circ}\text{F to } +174^{\circ}\text{F } (-40^{\circ}\text{C to } +79^{\circ}\text{C})$

ROHS Compliant Yes

Certification/Specification UL969

UL Recognized (US) Yes