

## Cooper Bussmann

[Homepage](#)  
[About Cooper Bussmann](#)  
[Contact Us](#)  
[Privacy](#)  
[Legal](#)  
[Cooper Bussmann® Brand](#)  
[Site Map](#)



## KTK-10

Fast-Acting Supplementary Fuse, 600V, 13/32 - 1-1/2 Inches

### Product Information

Product Type:	Fuse
Product Family:	Electrical Power
Upgrade Product:	<a href="#">LP-CC-10</a>
Brand:	Cooper Bussmann
Sub-brand:	Low-Peak

### Certifications

[UL Listed](#)  
[CSA Certified](#)

### Recommended Products

Rec. Fuse Block:	<a href="#">BM603 Series</a>
Rec. Inline Fuse Holder:	<a href="#">HEB Series</a>
Rec. Panel-mount Fuse Holder:	<a href="#">HPS Series</a>
Rec. Modular Fuse Holder:	<a href="#">CHM Series</a>
Rec. Fuse Clips:	<a href="#">5960 Series</a>
Rec. Cover:	<a href="#">SAMI-7 Series</a>

### Electrical Properties

Maximum AC Voltage:	600
Amperage Rating:	10
AC Interrupting Ratings:	<ul style="list-style-type: none"> <li>100000 at 600V</li> </ul>
Fast Acting:	Yes

### Physical Properties

Dimensions:	1.5in.(L) × 0.41in.(W) × 0in.(H)
-------------	----------------------------------


# LIMITRON®

## Fast-Acting Fuses

### 600 Volt, 1/10 - 30 Amps




#### Dimensional Data



- LIMITRON® fast-acting fuse.
- Melamine tube.
- Nickel-plated bronze endcaps.

#### Time-Current Characteristic Curves—Average Melt



**Catalog Symbol:** KTK

**Fast-Acting**

1/10 TO 30A

600Vac (or less)

**Interrupting Rating:** 100,000A RMS Sym. (UL)

UL Listed, STD. 248-14, (Guide #JDYX, File #E19180)

**CSA Certified:** C22.2 NO. 248.14

(File #53787—Class #1422-01)

HRC-MISC

#### Electrical Ratings (Catalog Symbol and Amperes)


600Vac - UL Listed and C.S.A.

KTK-1/10	KTK-1	KTK-6	KTK-25
KTK-1/8	KTK-1-1/4	KTK-7	KTK-30
KTK-2/10	KTK-1-1/2	KTK-7-1/2	—
KTK-1/4	KTK-2	KTK-8	—
KTK-3/10	KTK-2-1/2	KTK-9	—
KTK-4/10	KTK-3	KTK-10	—
KTK-1/2	KTK-3-1/2	KTK-12	—
KTK-6/10	KTK-4	KTK-15	—
KTK-3/4	KTK-5	KTK-20	—

#### Carton Quantity and Weight

Ampere Ratings	Carton Qty.	Weight*	
		Lbs.	Kg.
1-30	10	.180	.082

\*Weight per carton.



Recommended fuseblocks/fuseholders for 13/32" x 1-1/2" fuses  
See Data Sheets listed below

- Open fuseblocks - 1104, 2104
- Finger-safe fuseholders - 1109, 1102, 1103, 1151
- Panel-mount fuseholders - 2114, 2113, 2108, 2112, 2109, 2140
- In-line fuseholders - 2127, 2126

CE