


147 Central Avenue
 Hackensack, New Jersey 07601
 Tel: 201-489-8989 • Fax: 201-489-6911




CHICAGO MINIATURE LAMP, INC.
 WHERE INNOVATION COMES TO LIGHT

T-1 3/4 Wedge Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM11	2.5	.200	.200	1,000	C-2R
CM111	2.7	.100	.230	5	S-2
CM56	5.0	.115	.150	20,000	C-2R
CM79	6.0	.200	.600	1,000	C-2R
CM16	6.3	.150	.340	5,000	C-2F
CM84	6.3	.040	.030	20,000	C-2R
CM86	6.3	.200	.400	20,000	C-2F
CM18	14.0	.040	.130	5,000	C-2F
CM37	14.0	.090	.500	1,500	C-2F
CM70	14.0	.150	1.50	100	C-2F
CM73	14.0	.080	.300	15,000	C-2F
CM74	14.0	.100	.700	500	C-2F
CM17	28.0	.065	.650	5,000	C-2F
CM85	28.0	.040	.300	7,000	C-2F

T-1 3/4 Midget Screw Base



Part Number	Design Voltage	Amps	MSCP	Life Hours	Filament Type
CM8669	1.35	.060	.010	500	C-6
CM1767	2.50	.200	.200	500	C-2R
CM1769	2.50	.200	.200	500	C-2R
CM8693	2.70	.060	.040	6,000	C-2R
CM3153	5.00	.060	.150	5,000	C-2R
CM342	6.00	.040	.030	10,000	C-2V
CM1768	6.00	.200	.600	1,000	C-2R
CM7323	6.00	.200	.550	5,000	C-2R
CM378	6.30	.200	.400	20,000	C-2F
CM1775	6.30	.075	.230	1,000	C-2R
CM389	10.0	.040	.080	5,000	C-2F
CM373	14.0	.080	.500	1,500	C-2F
CM383	14.0	.080	.500	750	C-2F
CM8162	14.0	.100	.500	10,000	C-2F
CM8362	14.0	.080	.300	15,000	C-2F
CM8536	18.0	.040	.150	10,000	C-2F
CM335	28.0	.040	.340	4,000	C-2F
CM335LSV	28.0	.060	.340	25,000	C-2F
CM369	28.0	.040	.340	4,000	C-2F
CM399	28.0	.040	.300	7,000	C-2F
CM8369	28.0	.065	.650	15,000	C-2F
CM8384	28.0	.040	.150	10,000	C-2F

Chicago Miniature Lamp reserves the right to make specification revisions that enhance the design and/or performance of the product