

Path: [Home](#) > [Enclosure Index](#) > Sloped Steel & Aluminum Consoles



[click to enlarge](#)

[15 Degree Slope \(Steel Back\)](#)



[click to enlarge](#)

[15 Degree Slope \(Aluminum Back\)](#)



[click to enlarge](#)

[30 Degree Slope \(Aluminum Back\)](#)

### *Key Features:*

- 18 ga. steel base for extra strength
- Easy to machine - aluminum top panels are 0.064" thick aluminum.
- Sides include vertical rows of ventilation
- Sold pre-assembled with a two tone grey powder paint finish (base is dark satin gray, slope top is smooth light grey).
- Comes with four self adhesive rubber feet and required hardware.
- Replacement screws **1421J6** (Pkg. of 6, 6-32 Philips head screws).

### *15 Degree Slope (Aluminum Top Slope, Steel Base & Back)*






[click to enlarge](#)





Front View



[click to enlarge](#)

Rear View

Part Number	 PDF Reader File	AutoCAD .dwg Files (zipped)	Units	Dimensions			
				Width	Depth	Rear Height	Front Height
500-0930			inch	7.0	7.0	2.13	1.2
			mm	178	178	54	30

	41K	27K					
<b>500-0940</b>			inch	7.6	7.0	3.78	2.86
	41K	27K	mm	190	178	96	73
<b>500-0950</b>			inch	11.7	7.83	2.13	1.2
	41K	27K	mm	297	199	54	30












***15 Degree Slope  
(Aluminum Top Slope & Back, Steel Base)***



click to enlarge  
Front View



click to enlarge  
Rear View

Part Number	 Reader File	AutoCAD .dwg Files (zipped)	Units	Dimensions			
				Width	Depth	Rear Height	Front Height
<b>515-0910</b>			inch	4.50	6.0	2.13	1.13
			mm	114	152	54	29
<b>515-0920</b>			inch	6.0	6.0	2.13	1.13
			mm	152	152	54	29
<b>515-0930</b>			inch	7.4	6.0	2.13	1.13
			mm	188	152	54	29
<b>515-0940</b>			inch	7.4	6.0	3.78	2.78
			mm	188	152	96	71
<b>515-0950</b>			inch	11.7	7.7	2.13	1.2
			mm	297	196	54	30






***30 Degree Slope  
(Aluminum Top Slope & Back, Steel Base)***



click to enlarge  
Front View



click to enlarge  
Rear View

Part Number	 Reader File	AutoCAD .dwg Files (zipped)	Units	Dimensions			
				Width	Depth	Rear Height	Front Height
519-0910	 41K	 16K	inch	8.5	5.7	3.78	1.86
			mm	216	145	96	47
519-0920	 41K	 16K	inch	13.7	6.9	3.78	1.86
			mm	348	175	96	47

DOWNLOAD

catalog pages on this series (107K) [9C-500-519.pdf](#)