

DANTONA
INDUSTRIES, INC.
For all your battery needs!

Communication Batteries




DANTONA PART SEARCH



Dantona Part # LAP-270LI


Voltage: 10.8
Capacity: 4800
Composition: LION
Dimensions:
Connector:

LAPTOP/NOTEBOOK COMPUTER PACKS



| Part No. | Pic. # | Volts | Cap. | Size - Inches (L x W x H) | Termination |
|------------|--------|-------|------|------------------------------|----------------|
| LAP-251NMH | 7 | 12 | 3800 | 6.78 X 2.78 X .78 | 5 CONN ON END |
| LAP-252NMH | 2 | 14.4 | 3000 | 5.75 X 4.38 X .78 | 5 CONN ON END |
| LAP-253NMH | 12 | 9.6 | 3800 | 5.50 X 2.75 X .78 | 4 CONN ON END |
| LAP-254LI | 11 | 10.8 | 3200 | 3.25 X 2.75 X 1.375 | 11 CONN ON END |
| LAP-254NMH | 11 | 9.6 | 3800 | 3.25 X 2.75 X 1.375 | 11 CONN ON END |
| LAP-255NMH | 1 | 9.6 | 3800 | 4.125 X 4 X .75 | 4 CONN ON END |
| LAP-256LI | 10 | 14.4 | 3200 | 5.38 X 3.38 X 1 | 8 CONN ON END |
| LAP-257LI | 6 | 10.8 | 3200 | 4.75 X 3.75 X 1 | 4 CONN ON END |

| Part No. | Pic. # | Volts | Cap. | Size - Inches (L x W x H) | Termination |
|------------|--------|-------|------|------------------------------|---------------------------|
| LAP-258NMH | 13 | 7.2 | 1700 | 5.25 X .125 X .625 | 3 CONN ON SIDE |
| LAP-259LI | 14 | 10.8 | 2400 | 6.25 X 2.75 X .75 | 6 CONN ON END |
| LAP-260LI | 9 | 10.8 | 2400 | 8.0625 X 1.75 X .75 | 11 CONN ON END |
| LAP-261LI | 3 | 10.8 | 5600 | 6.50 X 2.75 X 1.0625 | 2 CONN ON BACK 10 ON SIDE |
| LAP-262LI | 5 | 14.4 | 3200 | 6 X 3.25 X .75 | 8 CONN ON END |
| LAP-263NMH | 8 | 12 | 3800 | 5.50 X 2.50 X 1.125 | 3 CONN ON SEND |
| LAP-264LI | 4 | 14.4 | 4800 | 5.50 X 4.38 X .75 | 5 CONN UNDER LATCH |



| Part No. | Pic. # | Volts | Cap. | Size - Inches (L x W x H) | Termination |
|------------|--------|-------|------|------------------------------|-----------------------------|
| LAP-265LI | 2 | 14.4 | 3200 | 6 X 3.25 X .75 | 8 CONN ON END |
| LAP-266LI | 12 | 14.4 | 3200 | 5.25 X 4.25 X .78 | 3 CONN ON END |
| LAP-267LI | 10 | 14.4 | 2700 | 5.50 X 3.50 X .75 | 2 ROWS OF 8 |
| LAP-268LI | 4 | 10.8 | 4050 | 8.50 X 2.187 X .78 | 6 CONN ON END |
| LAP-269LI | 6 | 14.4 | 2500 | 6 X 3 X .75 | "7 HOLES ON END, 2 LG 5 SM" |
| LAP-270LI | 5 | 10.8 | 4800 | 5.50 X 3.75 X .75 | 6 CONN ON END |
| LAP-271LI | 3 | 10.8 | 4800 | 5.75 X 3.50 X .75 | 6 CONN ON END |
| LAP-272LI | 9 | 14.4 | 3200 | 5.25 X 3.50 X .75 | 9 CONN ON END |
| LAP-273NMH | 11 | 10.8 | 1600 | 6.78 X 2.125 X .75 | 3 CONN ON END |

| Part No. | Pic. # | Volts | Cap. | Size - Inches (L x W x H) | Termination |
|------------|--------|-------|------|------------------------------|----------------|
| LAP-274LI | 13 | 10.8 | 3600 | 5 X 2.78 X 1 | 5 CONN ON END |
| LAP-275LI | 1 | 10.8 | 5400 | 5.78 X 3.50 X .75 | 6 CONN ON END |
| LAP-276NMH | 7 | 9.6 | 3500 | 6 X 3 X .75 | 9 CONN ON END |
| LAP-277LI | 15 | 10.8 | 3200 | 4.75 X 3.25 X 1 | 4 CONN ON END |
| LAP-278LI | 16 | 10.8 | 3200 | 5.25 X 2.75 X .75 | 9 CONN ON END |
| LAP-278NMH | 16 | 7.2 | 3800 | 5.25 X 2.75 X .75 | 9 CONN ON END |
| LAP-279LI | 8 | 10.8 | 4800 | 8.50 X 2.25 X .75 | 8 CONN ON SIDE |
| LAP-279NMH | 8 | 10.8 | 3800 | 8.50 X 2.25 X .75 | 8 CONN ON SIDE |
| LAP-280NMH | 14 | 10.8 | 3800 | 8.50 X 2.25 X .75 | 5 CONN ON SIDE |

COMPUTER