

DANTONA
INDUSTRIES, INC.
For all your battery needs!

Lead Acid Batteries




DANTONA PART SEARCH



Dantona Part # COMP-7-1

Voltage: 3
Capacity: 850
Composition: LITHIUM
Dimensions: 14.5MM X 25.0MM
Connector: SOLDER TABS

3V LITHIUM CYLINDRICAL CELLS



NUMBER BY CELL PICTURE CORRESPONDS TO PICTURE # IN GRID

PART NO.	X-REFERENCE	PIC #	VOLTS	CAP. mAh	DIMENSIONS(mm)		TERMINATION
					DIAMETER	HEIGHT	
LITH-28	BR425	1	3	25	4.2	25.9	-
LITH-29	BR435	1	3	50	4.2	35.9	-
COMP-15	CR1/3N	2	3	160	11.6	10.8	-
COMP-15-1	CR1/3N-T	2	3	160	11.6	10.8	1
COMP-15-2	CR1/3N-P	2	3	160	11.6	10.8	2
COMP-15-3	CR1/3N-FT	2	3	160	11.6	10.8	3
COMP-15-3VL	CR1/3N-FT3	2	3	160	11.6	10.8	3 (7.5MM)
COMP-7	CR14250SE	3	3	850	14.5	25.0	-
COMP-7-1	CR14250SE-T	3	3	850	14.5	25.0	1
COMP-7-2	CR14250SE-P	3	3	850	14.5	25.0	2
COMP-7-2P3	CR14250SE-P3	3	3	850	14.5	25.0	2
COMP-7-3	CR14250SE-FT	3	3	850	14.5	25.0	3
COMP-7-5	CR14250SE-SP1	3	3	850	14.5	25.0	5
COMP-3	CR12600SE	4	3	1400	12.0	60.0	-
COMP-3-1	CR12600SE-T	4	3	1400	12.0	60.0	1
COMP-3-2	CR12600SE-P	4	3	1400	12.0	60.0	2
COMP-3-3-7.5	CR12600SET-FT3	4	3	1400	12.0	60.0	3 (7.5MM)
COMP-3-3-10	CR12600SET-FT	4	3	1400	12.0	60.0	3 (10MM)
COMP-29	CR17335SE	5	3	1800	17.0	33.5	-
COMP-29-1	CR17335SE-T	5	3	1800	17.0	33.5	1
COMP-29-2	CR17335SE-P	5	3	1800	17.0	33.5	2
COMP-29-3	CR17335SE-FT	5	3	1800	17.0	33.5	3
COMP-5	BR2/3A	6	3	1200	17.0	33.5	-
COMP-5-1	BR2/3AT2SP	6	3	1200	17.0	33.5	1
COMP-5-2	BR2/3AP2SP	6	3	1200	17.0	33.5	2
COMP-5-3	BR2/3AE2SP	6	3	1200	17.0	33.5	3
COMP-5-5	BR-2/3AAX	6	3	1200	17.0	33.5	5

CELL TERMINATIONS

MATCH CELL PICTURE # WITH TERMINATION TO DETERMINE PART NO. IF NO TERMINATION IS INDICATED, CELL HAS PRESSURE CONTACT.

(1) FLAT SOLDER TAB FOR ATTACHING LEAD WIRE



(2) 2 PIN PC MOUNT SINGLE PIN EACH SIDE

