


Fan Panel

- Create your own 19" rack mount fan or filter fan panels
- Accepts standard square fans (available below or use your own)
- For a filter fan panel use our filter fan grills below
- Perfect for an intake fan panel. When using "push-pull" cooling use the fan grill panel below for exhaust
- Rugged textured black powder paint
- Requires mounting [hardware](#)
- Control your rack temperature with our [economical, compact thermostat](#)

Part Number	Number of Fan Holes	Accepts Fan Size	Panel Height	
			Inches	Units
PPFP190802BK1	2	3.15"	5.25	3
PPFP190803BK1	3	3.15"	5.25	3
PPFP191202BK1	2	4.70"	7.00	4




Fan Grill Panel

- Create your own 19" rack mount fan panels
- Accepts standard square fans (4.7" available below or use your own)
- Perfect as an exhaust fan panel when using "push-pull" cooling. Use the fan panel above, with filter grills for intake
- Rugged textured black powder paint finish
- Requires mounting [hardware](#)

- Control your rack temperature with our [economical, compact thermostat](#)

Part Number	Number of Fan Holes	Accepts Fan Size					Panel Height	
							Inches	Units
PPGP191202BK1	2	4.70"					5.25	3




Baffle Panel

- Standard 19" rack mount
- Rear sloping baffle for directing air flow
- Steel construction
- Shown here upside down, to show construction
- Extends apx. 14" behind panel rails
- Rugged, heat absorbing, black powder paint finish - smooth finish to match our standard panels
- Requires mounting [hardware](#)

Part Number	Color					Panel Height	
						Inches	Units
PVBB19001BK2	Black					1.75	1

BAFFLE PANEL


- Standard, 19" rack mount
- Rear sloping baffle for directing air flow
- 16 gauge steel construction
- Shown here, upside down to show construction
- Extends apx. 14" behind panel rails
- Smooth black powder paint finish to match our standard panels
- Requires mounting hardware



Part Number	Panel Height	
	Inches	Units
PVBB19001BK2	1.75	1

FAN PANELS

- Standard, 19" rack mount
- Create your own 19" rack mount fan or filter fan panels
- Accepts standard square fans (see our cooling accessory section or use your own)
- For a filter fan panel use our filter fan grills (see our cooling accessory section)
- Perfect as an intake fan panel (when using "push-pull" cooling use the fan grill panel below for exhaust)
- Rugged textured black powder paint
- Requires mounting hardware
- Control your rack temperature with our economical, compact thermostat (see our cooling accessory section)



Part Number	Number of Fan Holes	Accepts Fan Size	Panel Height	
			Inches	Units
PPFP190802BK1	2	3.15"	5.25	3
PPFP190803BK1	3	3.15"	5.25	3
PPFP191202BK1	2	4.7"	7.00	4

FAN GRILL PANELS

- Standard, 19" rack mount
- Create your own 19" rack mount fan panels
- Accepts standard square fans 4.7" (120 mm) see our cooling accessory section or use your own)
- Perfect for an exhaust fan panel (when using "push-pull" cooling use the fan panel above with filter grills for intake)
- Rugged textured black powder paint
- Requires mounting hardware
- Control your rack temperature with our economical, compact thermostat (see our cooling accessory section)



Part Number	Number of Fan Holes	Accepts Fan Size	Panel Height	
			Inches	Units
PPGP191202BK1	2	4.7"	5.25	3