

Filter Fans

Filtered Fan Boxes and Filter Grills





Filtered Fan Box

Description

- In a typical cooling arrangement, the filtered fan box pulls air into the enclosures and the filter grill is used as an air outlet.
- The washable aluminum filter grill and the air filter are easily accessible and can be removed for cleaning.
- The filtered fan boxes are available in either 115 VAC or 230 VAC, 50/60 Hz.
- Filtered passive ventilation can be provided by an exhaust filter for either convection cooling or in combination with a fan in forced air cooling.

Standards

UR/CUR/CE approved fan motors.

Features

- 115 VAC or 230 VAC, 50/60 Hz.
- 6 foot lead wires.

Filter Grill

- Exceptionally quiet operation.
- Versatile mounting and adaptability.
- Heavy-gauge steel construction.
- Attractive stainless steel grills.
- Shipped with air flow to pressurize. Can be user modified to exhaust.
- Aluminum filter is coated with adhesive baffle surfaces for dust and dirt collection. Can be recoated after cleaning for optimum performance.
- Drilling template included.
- NOTE: One grill and filter are included with each fan package. Normally, an additional exhaust grill and filter are required for each installation and must be ordered separately.

Accessories


- Filter coat...see page 367
- Replacement Filter...see page 367


Technical references and DXF downloads available at www.hammfg.com

All dimensions in inches unless specified otherwise



Filter Fans Filtered Fan Boxes and Filter Grills





Filtered Fan Boxes

Free Flow Air Delivery		RPM	Running											Ship	
Part No.	CFM	Volts	Nominal	Amps	Watts	Α	В	С	D	D¹	Е	F	G	Н	Wt. lbs
XF4115	105	115	3000	0.18	15	6.13	7.38	2.38	5.63	5.75	6.38	4.13	0.78	7.0	5
XF4230	105	230	3000	0.09	15	6.13	7.38	2.38	5.63	5.75	6.38	4.13	0.78	7.0	5
XF6115	220	115	3300	0.29	33	7.63	8.88	3.00	7.13	7.25	7.88	4.50	1.34	8.5	6
XF6230	220	230	3300	0.15	33	7.63	8.88	3.00	7.13	7.25	7.88	4.50	1.34	8.5	6
XF10115	5 560	115	1600	0.87	60	11.63	13.00	4.56	11.13	11.25	11.88	6.88	2.16	12.5	12
XF10230	560	230	1600	0.45	60	11.63	13.00	4.56	11.13	11.25	11.88	6.88	2.16	12.5	12

Exhaust Grill and Filters


Part No	Α	В	D	E¹	F¹	H¹
XFG4	6.13	7.38	5.63	6.38	4.13	7.00
XFG6	7.63	8.88	7.13	7.88	4.50	8.50
XFG10	11.63	13.00	11.13	11.88	6.88	12.50

¹ Dimension for mounting and cabinet cutout. Secure sheet metal with #8 hardware.

Replacement Filters

Part No	Pkg. Qty.
XFF4	3
XFF6	3
XFF10	3





Part No.	1475Q



Technical references and DXF downloads available at www.hammfg.com

All dimensions in inches unless specified otherwise