


## "Contempra 2" Rack Frame Side Panels



### Features:

-  **Sold in pairs**
- Constructed of 16 gauge steel
- Panels fit flush with frame
- Features quick release quarter turn cam fasteners (4 per side) with internal latching provision
- Finished in a rugged, textured powder paint
- For higher security, quarter turn fasteners can be replaced with key locking versions (see below). Order part number **CSPQTRL**



Assembly  
Instructions

### For use with 23.63" Deep Rack Frames

Part Number (Sold in Pairs)	Color		Drawing File Size		.zip file size	Frame Panel Height	
						Inches	Units
<b>CSP3523BK1</b> <b>CSP3523CG1</b>	Black Gray/Beige		86K		28K	<b>35</b>	20
<b>CSP4223BK1</b> <b>CSP4223CG1</b>	Black Gray/Beige		86K		28K	<b>42</b>	24
<b>CSP4923BK1</b> <b>CSP4923CG1</b>	Black Gray/Beige		86K		28K	<b>49</b>	28
<b>CSP5623BK1</b> <b>CSP5623CG1</b>	Black Gray/Beige		93K		38K	<b>56</b>	32
<b>CSP6323BK1</b> <b>CSP6323CG1</b>	Black Gray/Beige		93K		39K	<b>63</b>	36
<b>CSP7023BK1</b> <b>CSP7023CG1</b>	Black Gray/Beige		93K		38K	<b>70</b>	40

<b>CSP7823BK1</b> <b>CSP7823CG1</b>	Black Gray/Beige		93K		38K	<b>78.75</b>	45
<b>CSP8523BK1</b> <b>CSP8523CG1</b>	Black Gray/Beige		93K		39K	<b>85.75</b>	49

**For use with 31.5" Deep Rack Frames**

<b>Part Number</b> <b>(Sold in Pairs)</b>	<b>Color</b>		<b>Drawing</b> <b>File Size</b>		<b>.zip</b> <b>file size</b>	<b>Frame Panel Height</b>	
						<b>Inches</b>	<b>Units</b>
<b>CSP3531BK1</b> <b>CSP3531CG1</b>	Black Gray/Beige		86K		28K	<b>35</b>	20
<b>CSP4231BK1</b> <b>CSP4231CG1</b>	Black Gray/Beige		86K		28K	<b>42</b>	24
<b>CSP4931BK1</b> <b>CSP4931CG1</b>	Black Gray/Beige		86K		28K	<b>49</b>	28
<b>CSP5631BK1</b> <b>CSP5631CG1</b>	Black Gray/Beige		93K		38K	<b>56</b>	32
<b>CSP6331BK1</b> <b>CSP6331CG1</b>	Black Gray/Beige		93K		39K	<b>63</b>	36
<b>CSP7031BK1</b> <b>CSP7031CG1</b>	Black Gray/Beige		92K		38K	<b>70</b>	40
<b>CSP7831BK1</b> <b>CSP7831CG1</b>	Black Gray/Beige		93K		38K	<b>78.75</b>	45
<b>CSP8531BK1</b> <b>CSP8531CG1</b>	Black Gray/Beige		93K		39K	<b>85.75</b>	49

**For use with 36" Deep Rack Frames**

<b>Part Number</b> <b>(Sold in Pairs)</b>	<b>Color</b>		<b>Drawing</b> <b>File Size</b>		<b>.zip</b> <b>file size</b>	<b>Frame Panel Height</b>	
						<b>Inches</b>	<b>Units</b>
<b>CSP3536BK1</b> <b>CSP3536CG1</b>	Black Gray/Beige		86K		28K	<b>35</b>	20
<b>CSP4236BK1</b> <b>CSP4236CG1</b>	Black Gray/Beige		86K		28K	<b>42</b>	24
<b>CSP4936BK1</b> <b>CSP4936CG1</b>	Black Gray/Beige		86K		28K	<b>49</b>	28
<b>CSP5636BK1</b> <b>CSP5636CG1</b>	Black Gray/Beige		93K		38K	<b>56</b>	32
<b>CSP6336BK1</b> <b>CSP6336CG1</b>	Black Gray/Beige		93K		39K	<b>63</b>	36

<b>CSP7036BK1</b> <b>CSP7036CG1</b>	Black Gray/Beige		93K		38K	<b>70</b>	40
<b>CSP7836BK1</b> <b>CSP7836CG1</b>	Black Gray/Beige		93K		38K	<b>78.75</b>	45
<b>CSP8536BK1</b> <b>CSP8536CG1</b>	Black Gray/Beige		93K		39K	<b>85.75</b>	49

For higher security, the quarter turn fasteners on the side panels can be replaced with this key locking version.


Order part number **CSPQTRL**

Kit contains 4 quarter turn locks and 8 keys.  
Good for 1 rack (ie...2 locks per side panel)




Assembly  
Instructions





PART No. CSP7031



# Side Panels (C2 Series)

## SIDE PANELS



### FEATURES

- Sold in pairs
- Constructed of 16 gauge steel
- Panels fit flush with frame
- Designed for easy removal and installation
- Features quick release 1/4 turn cam fasteners (4 per side) with internal latching provision
- Two pins on the bottom of the frame allow for easy alignment & installation
- Finished in a rugged textured powder paint

### 23.63" Deep

Part Number		Depth (Inches)	Panel Height	
Black Textured	Beige Textured		Inches	Units
CSP3523BK1	CSP3523CG1	23.63	35.00	20
CSP4223BK1	CSP4223CG1	23.63	42.00	24
CSP4923BK1	CSP4923CG1	23.63	49.00	28
CSP5623BK1	CSP5623CG1	23.63	56.00	32
CSP6323BK1	CSP6323CG1	23.63	63.00	36
CSP7023BK1	CSP7023CG1	23.63	70.00	40
CSP7823BK1	CSP7823CG1	23.63	78.75	45
CSP8523BK1	CSP8523CG1	23.63	85.75	49

### 31.5" Deep

Part Number		Depth (Inches)	Panel Height	
Black Textured	Beige Textured		Inches	Units
CSP3531BK1	CSP3531CG1	31.50	35.00	20
CSP4231BK1	CSP4231CG1	31.50	42.00	24
CSP4931BK1	CSP4931CG1	31.50	49.00	28
CSP5631BK1	CSP5631CG1	31.50	56.00	32
CSP6331BK1	CSP6331CG1	31.50	63.00	36
CSP7031BK1	CSP7031CG1	31.50	70.00	40
CSP7831BK1	CSP7831CG1	31.50	78.75	45
CSP8531BK1	CSP8531CG1	31.50	85.75	49

### 36" Deep

Part Number		Depth (Inches)	Panel Height	
Black Textured	Beige Textured		Inches	Units
CSP3536BK1	CSP3536CG1	36.00	35.00	20
CSP4236BK1	CSP4236CG1	36.00	42.00	24
CSP4936BK1	CSP4936CG1	36.00	49.00	28
CSP5636BK1	CSP5636CG1	36.00	56.00	32
CSP6336BK1	CSP6336CG1	36.00	63.00	36
CSP7036BK1	CSP7036CG1	36.00	70.00	40
CSP7836BK1	CSP7836CG1	36.00	78.75	45
CSP8536BK1	CSP8536CG1	36.00	85.75	49

## SIDE PANEL LOCKS



- For higher security, the quarter turn fasteners on the side panels can be replaced with this key locking version
- Order part number **CSPQTRL**
- Kit contains 4 quarter turn locks and 8 keys.
- Good for 1 rack (ie...2 locks per side panel)

19" Rack Mount

Welded