

UK universal terminal blocks

Connectors for all disconnect terminal blocks in the UK series

- The ST-SI-UK 4 fuse connector for 5 x 20 mm cartridge fuse inserts is available with and without a LED
- The ST-BE component connector is available as an individual connector for two-pos. components and as a double connector



Fuse connector for 5 x 20 mm cartridge fuses



Component connector for 2- and 4-pos. components

Notes:
1) If the fuse is faulty, the downstream circuit is not off load.
2) Integrated: Diode 1N 4007, reverse voltage: 1300 V, maximum continuous current: 1.0 A
3) With single arrangement.
4) Integrated: B 250 C 1500 rectifier, reverse voltage: 600 V, nominal voltage: 250 V, nominal current: 1.5 A



	Technical data				Technical data			
	IEC	UL/CUL	CSA	IEC/EN 60079-7	IEC	UL/CUL	CSA	IEC/EN 60079-7
Rated data								
Rated voltage [V]	250	300	300	-	-	300	-	-
Nominal current/cross section [A]/[mm ²]	6.3/-	6.3/-	10/-	-	16/-	10/-	-	-
Rated cross section [mm ²]	-	-	-	-	-	-	-	-
Cross-section range AWG	-	-	-	-	-	30-14	-	-
General data								
Tightening torque [Nm]	-	-	-	-	0.5 - 0.6	-	-	-
Insulating material	PA	PA	PA	PA	PA	PA	PA	PA
Inflammability class according to UL 94	V2	V2	V2	V2	V2	V2	V2	V2
	Ordering data			Ordering data				
	Type	Order No.	Pcs./Pkt.	Type	Order No.	Pcs./Pkt.		
Description	Color							
Fuse connector for cartridge fuse inserts 5 x 20 mm, 26.5 mm high, max. 6.3 A	black	ST-SI-UK 4	0921011	50				
Fuse connector , for cartridge fuse inserts, 5 x 20 mm, 26.5 mm high, max. 6.3 A, with LED, for 5 - 15 V AC/DC ¹⁾	black	ST-SILED 12-UK 4	0921024	50				
With LED for 15 - 30 V AC/DC	black	ST-SILED 24-UK 4	0921037	50				
With LED for 30 - 60 V AC/DC	black	ST-SILED 60-UK 4	0921040	50				
With LED for 110 - 250 V AC/DC	black	ST-SILA250-UK 4	0921053	50				
Component connector , for switching on 2-pos. components in the basic terminal block, fixing at screw terminal points, 19 mm high, max. 16 A ²⁾	gray				ST-BE	2802316	10	
Component connector , to connect 2-pos. components into the basic terminal block, 19 mm high, with LED for 24 V AC/DC					ST-BE-LA 24	2802374	10	
With LED for 230 V AC/DC					ST-BE-LA230	2802387	10	
Component connector , to connect 2-pos. components into the basic terminal block, with diode 1N 4007, 19 mm high ²⁾					ST-1N4007	2802329	10	
Component connector , for 4-pos. components, two basic terminal blocks required per connector, 19 mm high	gray				ST-BE-VP	2802332	10	
Component connector , for 4-pos. components, two basic terminal blocks required per connector, with bridge rectifier B 250 C 1500, 19 mm high ⁴⁾					ST-B250C1500	2802345	10	
Isolating connector , 13.5 mm high, max. 16 A					ST-K 4	5025462	50	
	Accessories			Accessories				
Plug pliers , simplify the removal of the isolating connector from a closed row of terminal blocks					TZ	0306704	10	
Center groove labeling					ZB 6 (CLIPLINE catalog, part 2)			