

Label - US-EML (20X8) - 0800458

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)


Label, Card, white, Unlabeled, Can be labeled with: THERMOMARK CARD PLUS, THERMOMARK CARD, Mounting type: Adhesive, Lettering field: 20 mm x 8 mm



Why buy this product

- The US-EML ... and US-EMLC ... UniSheet labeling ranges include markers for marking operating equipment in electrical and system engineering
- The markers, which are supplied in uniform sheets, can be labeled quickly, easily, and cost-effectively using the THERMOMARK CARD
- The UC-EMLC ... labels can be peeled off and stuck back on without disintegrating
- The perforated markers and labels are easy to separate and can be easily fitted
- When used in conjunction with high-quality ink ribbons, they result in a highly resistant form of labeling that is suitable for harsh environments
- The US-EML ... material is UL-listed
- The sheets provide space for including function texts
- Low restoring forces mean that the labels can even be stuck onto uneven surfaces and edges

Key commercial data

Packing unit	10 pc
Minimum order quantity	10 pc
GTIN	 4 046356 606325
Weight per Piece (excluding packing)	4.86 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Length (b)	20 mm
Width (a)	8 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
---------------------------------	-------------------

General

Color	white
Components	free from silicone and halogen
Material	Polyester

Label - US-EML (20X8) - 0800458

Technical data

General

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	64
Number of individual labels per row	4

Classifications

eCl@ss

eCl@ss 4.0	24190218
eCl@ss 4.1	24190218
eCl@ss 5.0	27141137
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC001675

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Accessories

Accessories

Magazine

Magazine - THERMOMARK CARD-US-MAG1 - 5146451

Magazine for the THERMOMARK CARD printer, for accommodating US cards

