# Contents | Insulated BNCs | Clips & Insulators | Accessories & Probes | Insulated Test Accessories | Kits | Cross Reference



BU-00000-\* Part # color

\* 0 - Black 5 - Green 2 - Red 6 - Blue 4 - Yellow 9 - White

**TEST LEADS** 

1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 Page 7



#### BU-3156-C-00-0

### **Insulated Mini-Alligator Clips To Insulated BNC**

- Nickel-plated steel; PVC insulator (No. 31); jaw opening 3/16" (5mm).
- Red (+) clips have 2" (51 mm) lead wires.
- Black (-) clips have 7" (178 mm) lead wires.
- Molded "Y" block prevents seperation and corrosion.
- BNC Male Connector gold-plated center, silver-plated body.
- Shielded RG58C/U, MIL-C-17F.
- #20 AWG wire (41/36) tinned copper with 105°C PVC insulation.
- Product Data Sheet
- Send us your questions about this product

#### BU-3131-A-00-\*

## Insulated "Mini-Alligator" Clip-Both Ends

- Nickel-plated steel; jaw opens to 3/16" (4.7 mm).
- PVC clip insulator (No. 31).
- #20 AWG (41/36) tinned copper hook-up wire; with 105°C PVC insulation.
- Product Data Sheet
- Send us your questions about this product



Enlarge



#### BU-3180-E-00-\*

# Insulated "Mini-Alligator" Clip To 0.025" (0.6mm) Square Pin Receptacle

- Nickel-plated steel with PVC insulator (No. 31); jaw opens to 3/16" (4.7 mm).
- Pin Receptacle is copper–nickel–tin alloy 725.
- ABS housed, 0.000030" (0.00076 mm) gold-plated conductor.
- Hook-up Wire: #22 AWG (19/34) tinned copper with 105°C PVC insulation.
- Product Data Sheet
- Send us your questions about this product

### BU-4444-A-00-\*

## Stackable 0.080" (2.0 mm) Pin Plug-Both Ends

- Pin tip is 0.080" (2.0 mm) dia.; 0.500" (12.7mm) long.
- Tip jack accepts 0.080" (2.0 mm) dia. pin jack contact.
- Nickel-plated beryllium copper spring.
- ABS housing.
- Hook-up Wire: #20 AWG (41/36) tinned copper with 105°C PVC insulation.
- Product Data Sheet
- Send us your questions about this product



# Contents Next

Home Insulated BNCs Clips & Insulators Insulated Test Accessories

Accessories & Probes Kits Cross Reference

© 1999-2000 Mueller Electric Company. All rights reserved. Problems with the site should be reported to the webmaster.