

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0002092134](#)
Status: **Active**
Overview: Standard .093" Pin and Socket Connectors
Description: 2.36mm Diameter, Standard .093" Pin and Socket PC Tail Terminal, Series 1376, Male, with Tin (Sn) Plated Contact, Without Detent, Bag Packaged

Documents:

[Drawing \(PDF\)](#) [Packaging Specification PK-1190-003 \(PDF\)](#)
[Product Specification PS-02-09 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-1376-001 \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [1376](#)
 Application Power, Wire-to-Wire
 Comments PC Tail For Standard .093" Housing
 Crimp Quality Equipment Yes
 Overview [Standard .093" Pin and Socket Connectors](#)
 Product Name Standard .093"
 UPC 800753615427

Physical

Gender Male
 Material - Metal Brass
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.957/g
 Packaging Type Bag
 Plating min - Mating 2.540µm
 Plating min - Termination 2.540µm
 Termination Interface: Style Through Hole
 Wire Insulation Diameter 4.00mm max.
 Wire Size AWG N/A
 Wire Size mm² N/A

Solder Process Data


Duration at Max. Process Temperature (seconds) 005
 Lead-free Process Capability WAVE
 Max. Cycles at Max. Process Temperature 001
 Process Temperature max. C 235

Material Info

Engineering Number 1376-A(P909)L

Reference - Drawing Numbers

Packaging Specification PK-1190-003
 Product Specification PS-02-09, PS-1376-001
 Sales Drawing SD-1376-*



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/61/2018 (27 June
 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[1376 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Tool [11030006](#)

Extractor Tool [638240200](#)

for .093 and
 HCS-125 Product
 Series