



MASTER HEAT GUN REPLACEMENT PARTS

| ITEM NO. | UPC NO. | Model NO. | DESCRIPTION |
|----------|---------|------------|---|
| 1 | 35149 | ARM-542 | Armature, With Retaining Rings, 120V (A Models) |
| 1 | 35150 | ARM-543 * | Armature, With Retaining Rings, 220V |
| 1 | 35151 | ARM-607 | Armature, With Retaining Rings, 120V (HG-751B) |
| 2 | 35152 | BAS-103K | Brush & Spring (Kit of 2) |
| 3 | 35153 | BLW-001 | Blower Wheel |
| 4 | 35154 | BRC-005K | Brush Cap (Kit of 2) |
| 5 | 35155 | BRH-025K * | Brush Holder, 220V (Kit of 2) |
| 5 | 35156 | BRH-040K | Brush Holder, 120V (Kit of 2) |
| 6 | 35157 | BRU-089K | Brush (Kit of 2) |
| 7 | 35158 | BRY-141 | Upper Bearing Bracket |
| 8 | 35159 | BSY-005 | Stand |

| | | | |
|----|-------|------------|-------------------------------|
| 9 | 35160 | FLD-450 * | Field, 220V |
| 9 | 35161 | FLD-451 | Field, 120V (A Models) |
| 9 | 35162 | FLD-484 | Field, 120V (HG-751B) |
| 10 | 35163 | GRD-007 | Shutter Guard |
| 11 | 35166 | GRT-044 | Cable Guard, 120V |
| 12 | 35167 | GRT-045 | Cord Grip Insert, 120V (Pair) |
| 13 | 35169 | HAS-011K | Element, HG-501A |
| 13 | 35170 | HAS-012K * | Element, HG-202A |
| 13 | 35171 | HAS-013K * | Element, HG-302A |
| 13 | 35172 | HAS-014K * | Element, HG-502A |
| 13 | 35173 | HAS-015K | Element, HG-751 & HG-751A |
| 13 | 35174 | HAS-016K * | Element, HG-752A |
| 13 | 35178 | HAS-041K | Element, HG-301A |
| 13 | 35179 | HAS-042K | Element, HG-201A |
| 13 | 35180 | HAS-043K | Element, HG-751B |
| 14 | 35181 | HCA-001 | Housing and Cover Set |
| 15 | 35182 | HDE-013 | Handle |
| 16 | 35183 | INN-032 | Mica |
| 17 | 35184 | INN-101 | Barrier |
| 18 | 35185 | KNB-003 | Knob |
| 19 | 35186 | NAS-006 | Nozzle Assembly With Screen |
| 20 | 35187 | NUT-017K | Nut, Element (Kit of 2) |
| 21 | 35189 | PLT-281 | Switch Plate |
| 22 | 35190 | RIN-017 | Snap Ring |
| 23 | 35191 | RIN-026K | Retaining Ring (Kit of 2) |
| 24 | 35192 | RIN-032 | Ring |
| 25 | 35193 | SHL-004 | Nozzle Shield |
| 26 | 35194 | SPA-025 | Washer, Rubber Mounting |
| 27 | 35195 | SPG-029 | Spring |
| 28 | 35196 | SPG-049K | Spring, Brush (Kit of 2) |
| 29 | 35197 | SRW-141 | Screw, Clamp |
| 30 | 35198 | SRW-321 | Screw, Shoulder |

| | | | |
|----|-------|-----------|--|
| 31 | 35199 | SRW-344K | Screw, Handle (Kit of 2) |
| 32 | 35200 | SRW-345 | Screw, Housing |
| 33 | 35201 | SRW-346 | Screw, Element Mounting & Housing (Kit of 3) |
| 34 | 35202 | SRW-347K | Set Screw, Brush Holder (Kit of 2) |
| 35 | 35203 | SRW-348K | Screw, Switch Plate (Kit of 4) |
| 36 | 35205 | SRW-349K | Screw, Nozzle (Kit of 3) |
| 37 | 35206 | SRW-350K | Screw, Bearing Bracket (Kit of 2) |
| 38 | 35207 | SRW-351K | Screw, Ground & Lockwasher Kit |
| 39 | 35208 | SWH-019 | Switch, Snap-In Rocker |
| 44 | 35209 | TMB-003 * | Terminal Block |
| 40 | 35210 | WHR-003KA | Washer (Kit of 2) |
| 41 | 35219 | 35219 * | Cordset, 220V, European |
| 41 | 35220 | 35220 * | Cordset, 240V, Australian |
| 12 | 51090 | 51090 * | Cord Grip, 220V |
| 43 | 51101 | 51101 * | Strain Relief |
| 41 | 51211 | 51211 | Cordset, 120V, 15 Amp (201A, 301A, 501A, 751B) |
| 41 | 51212 | 51212 | Cordset, 120V, 20 Amp (HG-751A-C) |
| 41 | 51265 | 51265 | Cordset, 220V, USA |
| 42 | 51411 | 51411 | Label, Warning (All Models) |
| 42 | 51467 | 51467 * | Label, Warning (220V Models) |

* 220 / 240 Volt Models Only