Switchcraft®

Previous Page | Return to Index | Next Page

EH Series Audio/Video/Data Panel Mount Connectors



Switchcraft's newest line of connectors, the EH Series, offers a wide range of connectors all within a standard XLR housing. A single panel cut-out allows the end user to mount multiple formats including USB-A, USB-B, Firewire, S-VHS, 3.5mm stereo with normal circuit, MIDI, both 9 pin and 15 pin HD D-sub, plus RCA and BNC feed-thru's. Perfect for systems integration, pro audio, A/V, data, etc. The connectors conveniently mount into standard XLR diagonal hole knockouts, which allows the installer to easily combine the different formats into standard pre-knocked plates or racks without having to custom drill and tap a specific hole for a specific connector. You can also populate your own combination of EH connectors in Switchcraft empty QG rack panels or single and dual gang wall plates.

Click to view the New Product Bulletin for the EH Series

Broadcast Series

EH Connectors: USB, Firewire, SVHS, 9pin, and 15pin HD Dsub, 3.5mm Stereo, BNC, and RCA

E & EH Series Part Number Scheme

	Connector Type	Part No. Prefix	Solder Contact	Feedthru	Black Finish	Bagged w/4-40 Mounting Screws
--	----------------	--------------------	-------------------	----------	-----------------	----------------------------------

3.5MM Mono	EH35MMM	SC	N/A	В	PKG
3.5MM Stereo	EH35MMS	SC	N/A	В	PKG
SVHS	EHSVHS	N/A	2	В	PKG
PS/2 (AKA: mouse port / 6 Pin Din)	EH6MD	N/A	2	В	PKG
Firewire (EEE1394) Straight Wired	EHFW	N/A	2	В	PKG
Firewire EEE1394 Cross Wired	EHFWX	N/A	2	В	PKG
RCA	EHRCA	N/A	2	В	PKG
BNC	EHBNC	SC	2	В	PKG
~ BNC (Recessed Front)	EHBNC2R	N/A		В	PKG
BNC to RCA	EHBNCRCA			В	PKG
RCA to BNC	EHRCABNC			В	PKG
USB A to B	EHUSBAB			В	PKG
USB B to A	EHUSBBA			В	PKG
9 Pin DSUB Male to Male	EHDB9MM			В	
+ 9 Pin DSUB Male to Female	EHDB9MF			В	
9 Pin DSUB Female to Female	EHDB9FF			В	
15 Pin HD DSUB Male to Male	EHHD15MM			В	
+ 15 Pin HD DSUB Male to Female	EHHD15MF			В	
15 Pin HD DSUB Female to Female	EHHD15FF			В	

+ Reversible gender.

~ Connector is flush with the face of the housing. If no "B" suffix, all connectors come with nickel housing.

If no "PKG" suffix, all connectors come bulk.

Additional E & EH Series Connectors and Components







Click here for full line of E Series XLRs

Connector Type XLRs	Part No. Prefix	Solder Contact	Black Finish	Gold Pin	Bagged w/4-40 Mounting Screws
XLR Female 3 Pin	E3F	SC	В	AU	PKG

NPB 560A

Switchcraft[®] EH Series Audio/Video/Data



The EH Series by Switchcraft® is a complete line of audio, video, and data connectors built into standard panel-mount XLR housings. Custom combinations of EH Series connectors can be quickly and easily loaded into an empty 19-inch 1RU (1x16), 1.5RU (1x16), or 2RU (2x16) rack pre-punched with tapped 4-40 holes.

Switchcraft's EH Series is the fastest and most versatile way to create a custom panel or wall plate perfectly suited to meet the needs of any studio, broadcast facility, or systems integrator.

For more information, visit: http://www.switchcraft.com/products/560.html



Switchcraft[®] NPB 560A

ET Series Audio/Video/Dafa



EHSVHS2B



EH6MD2





EH35MMSSC



EHRCA2B



EH Series	1	2	3	4	5	6
Connector Description	Housing	Connector	Feedthru	Solder	Black Finish	Bagged with Mounting Screws
3.5MM Mono	EH	35MMM	N/A	SC	В	PKG
3.5MM Stereo	EH	35MMS	N/A	SC	В	PKG
SVHS	EH	SVHS	2	N/A	В	PKG
PS/2	EH	6MD	2	N/A	В	PKG
Firewire (EEE1394) Straight-Wired	EH	FW	2	N/A	В	PKG
Firewire (EEE1394) Cross-Wired	EH	FWX	2	N/A	В	PKG
RCA	EH	RCA	2	N/A	В	PKG
BNC	EH	BNC	2	SC	В	PKG
BNC (Recessed Front)	EH	BNC2R		N/A	В	PKG
BNC to RCA	EH	BNCRCA			В	PKG
RCA to BNC	EH	RCABNC			В	PKG
USB A to B	EH	USBAB			В	PKG
USB B to A	EH	USBBA			В	PKG
9-Pin DSUB Male to Male	EH	DB9MM			В	PKG
9-Pin DSUB Male to Female	EH	DB9MF			В	PKG
9-Pin DSUB Female to Female	EH	DB9FF			В	PKG
15-Pin HD DSUB Male to Male	EH	HD15MM			В	PKG
15-Pin HD DSUB Male to Female	EH	HD15MF			В	PKG
15-Pin HD DSUB Female to Female	EH	HD15FF			В	PKG

*Sample Part Number: EHBNC2PKG (BNC Feedthru, Black Housing, Bagged with 4-40 Screws)

*Male to female 9-Pin and 15-Pin DSUBS are user reversible to create female to male connectors.

*All Switchcraft EH Series connectors are fully compatible with blank QG Panels.

Series	Pins	Gender	Fas-Disconnect Option	Termination Style	Finish	Mounting Hole Options
E	3-5 Pins	M =Male F =Female	D =Fas-Disconnect Blank=Standard Locking	ST=Straight PC Terminals RA=Right Angle PC Terminals SC=Solder Cups Blank=Conical Springs (3-Pin Only)	B =Black Blank=Nickel	M3=M3x0.5 Thread 440=#4-40 Thread Blank=Counter-Sunk Hole



E3MSC



E3FSCB



E112BL

Connector Type	Part Number (Nickel Finish)			
1/4" Mono Locking Jack	E111L	E111BL		
1/4" Stereo Locking Jack	E112BL	E112BLB		

*For more information, go to: http://www.switchcraft.com/products/560.html



5555 N. Elston Avenue/Chicago, IL 60630 Phone: 773-792-2700 Fax: 773-792-2129