

WRIST STRAPS & COIL CORDS

Jewel® **ELASTIC ADJUSTABLE** WRIST STRAPS

09100 Wrist Strap, 6' Cord, Sapphire 09102 Wrist Strap, 6' Cord, Ruby 09103 Wrist Strap, 6' Cord, Topaz Wrist Strap, 6' Cord, Emerald 09104 Wrist Strap, 6' Cord, Amethyst 09110 Wrist Strap, 10' Cord, Sapphire 09130 Wristband Only, Sapphire 09105 Wristband Only, Ruby 09106 Wristband Only, Topaz 09107 09108 Wristband Only, Emerald 09109 Wristband Only, Amethyst 09140 Replacement Elastic Strip

09100 09102 09103 09104 999 9999 Drawings: 09105, 09150 **Technical Bulletin TB-2005** 9991 333 Listing #90P1

· High visibility

Bright colors allow supervisor to see that worker is wearing wrist strap

Patented* contoured spring supported banana plug Ensures reliable path-to-ground connection expanding banana plug into socket

· Solid stainless steel wrist band stud machined to exacting tolerances and precise profile

Ensures reliable path-to-ground connection to spring loaded 4mm stainless steel constant contact coil cord snap

- Lifetime warranty on our wrist band stud If damaged during normal use, will provide no-charge replacement
- Durable, lightweight fabric Some users prefer the softness, comfort and flexibility of this material

Made in America

For detailed information on all **Desco wrist straps:** www.desco.com/catalog

PREMIUM METAL EXPANSION WRIST STRAPS

09041 **Band Only**

09042 Band Only Extra Large 09085 Band with 6' Coil Cord

91070 Band with 6' Coil Cord & Angle Banana

· Premium metal expansion wrist strap Comfortable, designed not to pinch or pull hair

Patented* contoured spring supported banana plug Ensures reliable path-to-ground connection expanding banana plug into socket

Solid stainless steel wrist band stud machined to exacting tolerances and precise profile

Ensures reliable path-to-ground connection to spring loaded 4mm stainless steel constant contact coil cord snap

Superior contact with skin

For reliable removal of generated static charges

Adjustment band changes quickly and easily to any size One size fits all; only one item number to purchase and stock no "extra" links to lose

Made in America

Circumference - Regular: 5.5" - 13", Extra large: 6.25" - 14.5"

Drawings 09041, 09480, and 91095, Technical Bulletin TB-2005

NOTE: All bands on this page have a 4mm snap stud. Wrist strap kits include an alligator clip (excluding right angle products).

*US Patent 5951337

ANSI/ESD S20.20 Paragraph 6.2.2.1 Personnel Grounding Requirement "All personnel shall be bonded or electrically connected to ground or contrived ground when handling ESD sensitive items. When personnel are seated at ESD protective workstations, they shall be connected to the common point ground via a wrist strap system.'

Web Site: www.desco.com • Phone: (909) 627-8178 • Fax: (909) 627-7449


PREMIUM METAL EXPANSION **FIXED SIZE WRIST STRAPS**

09045 Band Only, Small 09044 Band Only, Medium 09043 Band Only, Large

09088 09087 Band with 6' Coil Cord. Medium 09086 Band with 6' Coil Cord, Large

Drawings 09043 and 09480











09085



WRIST STRAPS & COIL CORDS

ELASTIC ADJUSTABLE WRIST STRAPS

09028 Band Only

09070 Band with 6' Black Coil Cord 09069 Band with 12' Black Coil Cord 09029 Elastic Replacement Strip 09031 Replacement Clasp Only

- · Extra wide, soft elastic band Increased wearer comfort
- Has silver impregnated nylon knitted on inside for superior conductivity

Reliably removes generated static charges

Adjustable

Only one item to stock; may be fitted to almost all people

Locking clasp

Band locked so it will not slip

Made in America

Circumference - 2.5" - 13"

Drawings 09028, 09480, and 14010, Technical Bulletin TB-2005

LIGHTWEIGHT ELASTIC ADJUSTABLE WRIST STRAPS

Band with 6' Coil Cord 14830 Band with 10' Coil Cord

14840 Band Only

· Durable, lightweight fabric

Some users prefer the softness, comfort and flexibility of this material

· Has silver impregnated nylon knitted on inside for superior conductivity

Reliably removes generated static charges

Adjustable

Only one item to stock; may be fitted to almost all people

- Unique patented (US Patent 4,662,695) adjustment design eliminates exposed conductive "tail" of band Provides added safety, eliminating chance of providing inappropriate ground path
- Made in America

Circumference - 2.5" - 14"

Drawings 14810 and 14010, Technical Bulletin TB-2005

HOOK & LOOP WRIST STRAPS

09060 Band Only

Band with 6' Coil Cord 09078

· Non reactive, anti-microbial, anti-bacterial medical grade conductive strip

Reduces growth of mold, mildew, and fungus; the best choice for users with ultra sensitive skin

- Return loop, quick, easy adjustment mechanism One size fits all; only one item to purchase and stock
- Sewn inner conductive surface with no exposed conductive materials on exterior

Provides added safety eliminating chance of providing inappropriate ground path

- · Molded plastic cover Provides stable base for cord attachment
- Made in America

Drawings 09060 and 09480, Technical Bulletin TB-2005

NOTE: All bands on this page have a 4mm snap stud.





Listing #90P1 Complete wrist strap kits include an alligator clip.



WRIST STRAPS & COIL CORDS

Jewel®

RAPID RETRACTION COIL CORDS

 09120
 Coil Cord, 6', Sapphire

 09122
 Coil Cord, 6', Ruby

 09124
 Coil Cord, 6', Topaz

 09126
 Coil Cord, 6', Emerald

 09128
 Coil Cord, 6', Amethyst

 09121
 Coil Cord, 10', Sapphire

 09150
 Coil Cord, Right Angle, 6'

09150 Coil Cord, Right Angle, 6', Sapphire09151 Coil Cord, Right Angle, 10', Sapphire

High visibility

Bright colors allow supervisor to see that worker is wearing wrist strap

 Superior strain relief tests in excess of 50,000,000 cycles per ESD S1.1 - See Bending Life Test (exceeds by over 3,100 times the minimum requirement) Eliminates intermittent failures that occur with less durable single and dual wire cords

Patented* contoured spring supported banana plug
 Ensures reliable path-to-ground connection expanding banana plug into socket

Rapid retraction strength polyurethane coil cords
 Provides high memory and less coil cord dragging on work surface

Made in America

Drawings: 09120, 09150, Technical Bulletin TB-2005

RELAXED RETRACTION COIL CORDS

 09480
 Coil Cord, 6', Black

 09680
 Coil Cord, 12', Black

 09682
 Coil Cord, 20', Black

 91095
 Coil Cord, Right Angle,

91095 Coil Cord, Right Angle, 6', Black
14113 Coil Cord, Banana-Banana, 12', Black
14114 Coil Cord, Banana-Banana, 20', Black

Relaxed retraction strength black PVC
 More comfortable; will not interfere with wearer's movements

 Superior strain relief tests in excess of 1,000,000 cycles, per ESD S1.1 - See Bending Life Test (exceeds by over 62 times the minimum requirement)

Eliminates intermittent failures that occur with less durable single and dual wire cords

Improved snap design
 Stronger strain relief and snap retention for long life; low profile keeps cord from being disconnected

Banana plug molded at 90° on item 91095, creating low profile

Cords are less likely to be accidentally pulled out, eliminating time where a damaging static discharge event might occur

 Banana plugs on both ends of coil cord on items 14113 and 14114

Allows cart users to ground carts to common grounding point on bench

Made in America

Drawings 09480, 91095, and 14113, Technical Bulletin TB-2005

Per ESD Handbook TR20.20 paragraph 5.3.2.2.2 Wrist Strap Ground Cord, "At first glance, the ground cord appears to be a relatively simple assembly. However, the design requirements are considerable, given the wide range of user applications and the durability requirements of constant tugging, flexing, and dragging over the edge of workstation tops and equipment chassis."









See our products being
Made in America
on our web site:
www.desco.com/factory

*US Patent 5951337