

# SMOCKS AND GLOVES

# STATSHIELD® SMOCKS

### STATSHIELD® JACKETS WITH CUFFS


<u>Size</u>	<b>BLUE</b>	<b>WHITE</b>	<b>TEAL</b>
X Small	73749	73830	73850
Small	73750	73831	73851
Medium	73755	73832	73852
Large	73760	73833	73853
X Large	73765	73834	73854
2X Large	73770	73835	73855
3X Large	73771	73836	73856
4X Large	73772	73837	73857
5X Large	73773	73838	73858
6X Large	73774	73839	73859

## STATSHIELD® LAB COATS WITH CUFFS

<u>Size</u>	<u>BLUE</u>	<u>WHITE</u>	<u>TEAL</u>
X Small	73610	73630	73650
Small	73611	73631	73651
Medium	73612	73632	73652
Large	73613	73633	73653
X Large	73614	73634	73654
2X Large	73615	73635	73655
3X Large	73616	73636	73656
4X Large	73617	73637	73657
5X Large	73618	73638	73658
6X Large	73619	73639	73659

- · Conductive knitted cuff Eliminates need for wristband
- Creates Faraday Cage effect Charges on worker clothing shielded, protecting ESDS devices
- Patented\* hip-to-cuff grounding Allows your coil cord to snap to the hip of the smock for hands-free grounding, increasing productivity
- 9% minimum carbon conductive nylon fibers woven in chain-link design
- Provides continuous and consistent charge dissipation · Panel to panel conductivity
- Prevents isolated charged conductor in ESD protected area 2 years or 100 launderings
- See limited warranty on line at www.desco.com
- >10<sup>5</sup> ohms RTT
- Made in America

### **Technical Bulletin TB-2055**



Premium Statshield® Smocks feature our patented\* Hip-to-Cuff grounding feature for hands-free grounding. This removes charges from the worker while allowing hands to be free, allowing for increased productivity.

Web Site: www.desco.com • Phone: (909) 627-8178 • Fax: (909) 627-7449

Color:

For detailed information on all Desco smocks and gloves: www.desco.com/catalog





\*U.S. Patent #4,596,053

See our products being Made in America on our web site: www.desco.com/factory





# SMOCKS AND GLOVES

# 73882

Size	CHEST	<b>SLEEVE</b>
X Small	30"-32"	33 3/4"
Small	34"-36"	34"
Medium	38"-40"	34 3/8"
Large	42"-44"	35"
X Large	46"-48"	35 1/2"
2X Large	50"-52"	35 1/2"
3X Large	54"-56"	37 1/2"
4X Large	58"-60"	36 1/2"
5X Large	62"-64"	36"
6X Large	66"-68"	36"

# **ECONOMY SMOCKS**

<u>Size</u>	RLUE
X Small	73880
Small	73881
Medium	73882
Large	73883
X Large	73884
2X Large	73885
3X Large	73886
4X Large	73887
5X Large	73888
6X Large	73889

· Elastic in sleeve end connects conductive fabric to user's skin; path to ground requires use of regular wrist strap or foot grounder

Less expensive smock for use when premium features are not required

- Same fabric as premium product
- Identical weight, charge decay, and durability
- Made in America

**Technical Bulletin TB-3008** 

# STATIC DISSIPATIVE GLOVES

68105	Man's Small, Beige	
68104	Man's Medium, Blue	
68103	Man's Large, Brown	
68106	Man's Extra Large, Grey	
68102	Woman's Small, Pink	
68101	Woman's Medium, Red	
68100	Woman's Large, Orange	

Non-allergenic polyester glove

Comfortable, antistatic; low tribocharging material will conduct charges to ground

Installed 4mm snap stud

Attaches to coil cord; eliminating need for wristband

RTG 105 - 107

Can be tested with standard wrist strap testers

- Color coded, numerous sizes available Better fit provides high tactile sensitivity; size easily identified
- · Made in America

Drawing 68100



Our gloves eliminate the

need for wristbands and

help prevent Charged

68111 Medium **68110** Large

• Non-allergenic polyester glove

Comfortable, antistatic, low tribocharging material will conduct charges to ground

Nomex® lining

Operator can handle objects to a temperature of 200°F maximum

 Installed 4mm snap stud Attaches to coil cord

RTG 105 - 107

Can be tested with standard wrist strap tester

Unisex sizes

Versatile, with minimum inventory

Made in America

Drawing 68110

