

# Switchcraft®

[Previous Page](#) | [Return to Index](#) | [Next Page](#)



## Q-G® CORD PLUG CONNECTORS

### 1. R(\*)FZ CORD PLUG

- 2. R(\*)MZ CORD PLUG**
- 3. P(\*)F MICROPHONE PLUG**
- 4. P(\*)M GOOSENECK PLUG**

[click here to download a schematic drawing](#)

(you will need to have Adobe Acrobat installed on your system to do this)



**R(\*)FZ FEMALE CORD PLUG**

Right angle, female cord mount plug, latching. New style incorporates an insert that can rotate every 45° for added flexibility in tight applications. Also utilizes the new strain relief system with twist-on handle.

<b>Part Number <sup>1</sup></b>	<b>Insert Contacts</b>
R3FZ	3
R4FZ	4
R5FZ	5
R6FZ	6
R7FZ	7

**R(\*)M MALE CORD PLUG**

Right angle, male cord mount plug, latching. New style incorporates an insert that can rotate every 45° for added flexibility in tight applications. Also utilizes the new strain relief system with twist-on handle.

<b>Part Number<sup>1</sup></b>	<b>Insert Contacts</b>
R3MZ	3
R4MZ	4
R5MZ	5
R6MZ	6
R7MZ	7

## P(\*)F FEMALE MICROPHONE PLUG

Female microphone plug for gooseneck mount. Fits standard gooseneck with external 5/8-27 thread. Microphone plugs directly into connector. (Gooseneck not supplied.)

Part Number <sup>1</sup>	Insert Contacts
P3F	3
⌘P4F	4
⌘P5F	5

## P(\*)M MALE GOOSENECK PLUG

Male plug for gooseneck mount. Fits standard gooseneck with internal 5/8-27 thread. Use on gooseneck with microphone plug on opposite end. Plugs directly into female receptacle. (Gooseneck not supplied.)


Part Number <sup>1</sup>	Insert Pins
P3M	3
⌘P4M	4
⌘P5M	5

<sup>1</sup> Satin Nickel Finish. (standard)

⌘ Available on special order only; contact Switchcraft for price and delivery.


[Previous Page](#) | [Return to Index](#) | [Next Page](#)

**To search a category please click on the corresponding icon:**



Q-G® CONNECTORS (continued) **R(\*)FZ CORD PLUG**

Right angle, female cord mount plug, latching. New style incorporates an insert that can rotate every 45° for added flexibility in tight applications. Also utilizes the new strain relief system with twist-on handle.




Part Number	Insert Contacts
R3FZ	3
R4FZ	4
R5FZ	5
R6FZ	6
R7FZ	7

Accepts cable O.D.'s .100"-.285"  
For black finish, add "B" suffix.  
For black/gold finish, add "BAU" suffix.

**R(\*)MZ CORD PLUG**

Right angle, male cord mount plug, latching. New style incorporates an insert that can be rotated every 45° for added flexibility in tight applications. Also utilizes the new strain relief system with twist-on handle.




Part Number	Insert Pins
R3MZ	3
R4MZ	4
R5MZ	5
R6MZ	6
R7MZ	7


Accepts cable O.D.'s .100"-.285"  
For black finish, add "B" suffix.  
For black/gold finish, add "BAU" suffix.

**P(\*)F MICROPHONE PLUG**

Female microphone plug for gooseneck mount. Fits standard gooseneck with external 5/8-27 thread. Microphone plugs directly into connector. (Gooseneck not supplied.)




Part Number <sup>1</sup>	Insert Contacts
P3F	3
◇P4F	4
◇P5F	5



- Satin Nickel Finish. (standard)
  - Large flex relief accepts cable from .25" to .328" diameter. (optional)
  - Gold-plated contacts. (optional)
- ◇ Available on special order only; contact Switchcraft for price and delivery.

**P(\*)M GOOSENECK PLUG**

Male plug for gooseneck mount. Fits standard gooseneck with internal 5/8-27 thread. Use on gooseneck with microphone plug on opposite end. Plugs directly into female receptacle. (Gooseneck not supplied.)



Part Number <sup>1</sup>	Insert Pins
P3M	3
◇P4M	4
◇P5M	5

DIMENSIONS ARE FOR REFERENCE ONLY  $\frac{\text{Inch}}{\text{(mm)}}$