

**Xcelite
ErgoCrimp Plus® Crimping Tool Frame**



Product Details

Catalog No.	ECP000
UPC Code	037103059338
Crimping Range	Assorted
Connector Type	Assorted
Wire or Cable Size/Type	Assorted
Die Set	None
Packaging	Industrial Box/Carton
Tech. Spec.	Crimping Stripping Tools.pdf
Low Res. Image	ECP000_100.jpg
High Res. Image	ECP000_300.jpg
Operating Ins.	Crimp Tools Instructions.pdf
Stock Item	Normal Stock Item

Package Details (Dimensions)

Product Features:

- Patented ergonomic design makes this tool easy and comfortable to use
- Lowest possible handle forces required
- High quality construction with tight tolerances
- Superior crimp die design insures the highest quality crimp results
- High strength through-hardened alloy steel and precision manufacturing
- Guaranteed for 50,000 cycles
- Precise eccentric adjustment for consistent performance for life of tool
- Used with D100 through D111 die sets

Xcelite
ErgoCrimp Plus® Crimping Tool Frame



Individual Product	
Catalog No.	ECP000
UPC Code	037103059338
Quantity	1
Length (Inches)	13.25
Width (Inches)	5
Height (Inches)	1
Gross Weight (lb)	1.4
Volume (cu in)	66.25

Catalog No.	ECP000
I 2 of 5 Code	20037103059332
Quantity	25
Length (Inches)	17.5
Width (Inches)	13.3
Height (Inches)	12.5
Gross Weight (lb)	35
Volume (cu in)	2909.375

Crimping and Stripping Tools

Xcelite® ErgoCrimp Plus®

	<p>The ErgoCrimp Plus® is the world's most advanced crimping tool. It's patented design provides up to 50% better mechanical gain than any other tool, which results in the lowest handle forces possible. It can handle the widest range of crimping applications. The ErgoCrimp Plus® can be ordered with or without die sets installed.</p>
---	--

Catalog No.	Description
ECP000	CRIMP TOOL, ERGO, FRAME ONLY, NO DIE SET
ECP100	CRIMP TOOL, ERGO, INSUL 22-10 TERMINAL
ECP101	CRIMP TOOL, ERGO, NON-INSUL, 22-10 TERM
ECP102	CRIMP TOOL, ERGO, RG58/59/62, BNC/TNC
ECP104	CRIMP TOOL, ERGO, RG59/8281, 50/75 OHM
ECP105	CRIMP TOOL, ERGO, RG174 BNC/TNC
ECP106	CRIMP TOOL, ERGO, RG8/11/213/216, ETHERNET
ECP107	CRIMP TOOL, ERGO, RG6 & RG59 CATV COAX
ECP109	CRIMP TOOL, ERGO, SMA/SFR FIBER OPTIC
ECP110	CRIMP TOOL, ERGO, RJ-45 MODULAR PLUGS
ECP111	CRIMP TOOL, ERGO, RJ-11 MODULAR PLUGS
ECP112	CRIMP TOOL, ERGO, COMM, 20-10AWG (NO REPLACEMENT DIE SET)
D100	DIE SET, ERGO INSU 22-10 TERMINALS
D100A	DIE SET, ERGO INSU 22-10 ASSYMETRIC
D101	DIE SET, ERGO NON-INSUL 22-10AWG TERMINAL
D102	DIE SET, ERGO RG58/59 UA/BNI/INC CONNECT
D104	DIE SET, ERGO RG59/8281 50/75 OHM CENTER
D105	DIE SET, ERGO RG174 BNC/TNC
D106	DIE SET, ERGO RG8, RG11, RG213, RG216, ETHER
D107	DIE SET, ERGO RG59, RG6, CATV F CONNECTORS
D109	DIE SET, ERGO SMA/SFR FIBER OPTIC (D111)
D110	DIE SET, ERGO RJ45 MODULAR PLUGS
D111	DIE SET, ERGO RJ11 MODULAR PLUGS

Xcelite® Mini-Crimper

	<p>The Mini-Crimper is the smallest, lightest, and most ergonomic crimp tool specially designed for lower force applications. Its ergonomically designed handles and small open handle span make it extremely easy to use for end users with small hands</p>
---	--

Catalog No.	Description
MIC2616	CRIMP TOOL, INSUL, 26-16AWG
MIC3020BL	CRIMP TOOL, OPEN BARREL, D-SUB
MICPZD3	CRIMP TOOL, WIRE FERRULES, 22-10 AWG