

# **Reflex™ Super T-Stripper Wire Stripper**

## Catalog # 45-618



### **Features**

- Wire range #8 to #14 solid, #8 to #16 stranded
- 6-32 and 8-32 self-chasing screw-cutting holes
- Ergonomic handle design for maximum comfort
- Curved handles reduce wrist fatigue
- Sleeves extend forward to cushion thumb and fingers
- Textured sleeves with extra cushioning for added comfort
- Locking latch for safe storage

# Engineered to strip every wire right



#### Kinetic™ Reflex™ T®-Stripper Wire Stripper

Ergonomic handles with Santoprene™ grip and Thumb Valley™make this the premier wire stripper in the market.

#### Kinetic<sup>™</sup> Super Wire Stripper

The ergonomic design and patented Santoprene™ grip wicks away perspiration and reduces muscle fatigue. The Thumb Valley™ guide and precision stripping holes promote the highest accuracy in the industry.



- Thumb Valley Protection Pocket Locket Locking Hasp
- Shear Cut **Bolt Cutters**
- Santoprene™ Curved Handles

## Reflex™ Super T®-Stripper Wire Stripper

The ergonomic design with curved handles reduces wrist fatigue. Features 6/32 and 8/32 self-chasing, bolt cutting holes and a locking pawl for safe storage.



Designed for total-comfort and wire stripping. Ergonomic handles fit an electrician's natural grip and reduces hand fatigue. Textured, slipresistant sleeves cushion thumb and fingers.



Textured Comfort Ergo Handles

Locking Pawl

**Bolt Cutting** 

Extended

Extended Textured Ergo Handles



- Thumb Valley Protection
- Pocket Locket Locking Hasp
- Shear Cut **Bolt Cutters**
- Santoprene<sup>™</sup>
- Ergo Handles

#45-900's

45-915

45-918

#### Super T®-Stripper Wire Stripper

The industry standard for almost 50 years. Compact,

lightweight and easy to use. Features precision-ground,

knife-type blades, built-in looping holes, wire cutters

T®-Stripper Wire Stripper

and a convenient plier nose.

Traditional T®-Stripper Wire Stripper features with the added convenience of bolt-cutting holes and locking pawl. Curved comfort-grip handles accommodate high-volume wire stripping.



- Locking Pawl
- · Bolt Cutting
- Comfort
- Curved

٠			,	· · ·		-	,,,,					•	Straight Handles		Handles			
T®-\$														7				
6 a	3 10 0 12	0 12 2 14	14 16	16 18	18 20	20 22	22 24	24 26	26	28 30	30 32	Hole Size		#45-100's	#45 -300's	#45-400's	#45-600's	#45-700's
	T						22	24	26	28	30	Solid		45-125	45-317	45-417		
	T	T		Г		Γ	24	26	28	30	32	Stranded	A SANCE OF STREET	40-120	40-317	40-417	_	_
	T	T	14	16	18	П	22	П	П	Γ		Solid	Serenay	45-121	45-316	45-416	45-616	45-716
			16	18	20	22	24	26				Stranded	A Saintes	43-121	45-510	43-410	45-010	45-710
	10	12	14	16	18					Π		Solid	The second secon	45-120		45-415		45-715
	12	2 14	16	18	20					Γ		Stranded	i li	40-120	_	40-410	_	40-710
8	3 10	12	14	16				Γ		Γ		Solid	A A A A A A A A A A A A A A A A A A A	_	45-315		45-615	_
1	0 12	2 14	16	18		Γ		Γ		Γ		Stranded		_	40-010	_	40-010	_
6 8	3 10	12	14					Γ		Γ		Solid	THE RESERVE OF THE PERSON OF T	45-124	45-318	45-418	45-618	4E 740
8 1	0 12	2 14	16	Г						Γ	Π	Strand		45-124	40-010	45-410	45-010	45-718

45-123

Static Disp

## **Tools and Totes**



- Non-slip Santoprene™ textured grips
- Plier nose for holding and twisting wires
- Slide lock for safety and storage
- Thumb and finger valley makes stripping easier and more accurate
- "Shear-Cut™" bolt cutters

Description	Solid	Stranded	Cat. No.
Kinetic Super™ Wire Stripper	10-18	12-20	45-715
Kinetic Super™ Wire Stripper	14-24	16-26	45-716
Kinetic Super™ Wire Stripper	6-14	8-16	45-718

### Reflex™ Premium T®-Stripper Wire Strippers



- Ergonomic design for maximum comfort
- Curved handles reduce wrist fatigue
- Sleeves that extend to stripping head to cushion thumb and fingers
- Textured, no-slip sleeves provide a sure, easy grip

Description	Solid	Stranded	Cat. No.
Reflex™ Premium T®-Stripper Wire Stripper	10-18	12-20	45-415
Reflex™ Premium T®-Stripper Wire Stripper	14-24	16-26	45-416
Reflex™ Premium T®-Stripper Wire Stripper	22-30	24-32	45-417
Reflex™ Premium T®-Stripper Wire Stripper	6-14	8-16	45-418
Reflex™ Premium T®-Stripper – Metric	0.5mm²-	-4.0mm²	45-425-341
Reflex™ Premium T®-Cutter	Cu	tter	45-423

Kinetic™ Reflex™ T®-Stripper Wire Strippers



- Non-slip Santoprene™ textured grips and thumb rest
- Plier nose for holding and twisting wires
- Slide lock for safety and storage
- Thumb and finger valley makes stripping easier and more accurate
- "Shear-Cut™" bolt cutters

Description	Solid	Stranded	Cat. No.
Kinetic™ Reflex™ T®-Stripper Wire Stripper	10-18	12-20	45-915
Kinetic™ Reflex™ T®-Stripper Wire Stripper	6-14	8-16	45-918



- 6/32 and 8/32 self-chasing screw-cutting holes
- Locking pawl for safe storage
- Ergonomic design for maximum comfort
- Curved handles reduce wrist fatigue
- Sleeves that extend to stripping head to cushion thumb and fingers
- Textured sleeves with extra cushioning for added comfort

Description	Solid	Stranded	Cat. No.
Reflex™ Super T®-Stripper Wire Stripper	8-16	10-18	45-615
Reflex™ Super T®-Stripper Wire Stripper w/static dissipative grips	14-24	16-26	45-616
Reflex™ Super T®-Stripper Wire Stripper	8-14	8-16	45-618
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	12-2 and 14-2	_	45-621
Reflex™ Super 12/3 & 14/3 NM Cable T®-Stripper Wire Stripper	12-3 and 14-3	_	45-622