

T-5 T-Stripper Wire Stripper

Catalog # 45-120



Features

- Wire range #10 to #18 AWG solid, #12 to #20 AWG stranded
- Form-ground, hardened, knife-type blades for accurate stripping
- Tough steel construction
- Built-in wire cutter and wire looping holes
- Plier nose for extra gripping strength
- Laser-etched wire gauge markings
- Spring-loaded automatic opening
- · Corrosion-resistant, black oxide finish

Engineered to strip every wire right



Kinetic™ Reflex™ T®-Stripper Wire Stripper

Ergonomic handles with Santoprene™ grip and Thumb Valley™make this the premier wire stripper in the market.

Kinetic[™] Super Wire Stripper

The ergonomic design and patented Santoprene™ grip wicks away perspiration and reduces muscle fatigue. The Thumb Valley™ guide and precision stripping holes promote the highest accuracy in the industry.



- Thumb Valley Protection Pocket Locket Locking Hasp
- Shear Cut **Bolt Cutters**
- Santoprene™ Curved Handles

Reflex™ Super T®-Stripper Wire Stripper

The ergonomic design with curved handles reduces wrist fatigue. Features 6/32 and 8/32 self-chasing, bolt cutting holes and a locking pawl for safe storage.



Designed for total-comfort and wire stripping. Ergonomic handles fit an electrician's natural grip and reduces hand fatigue. Textured, slipresistant sleeves cushion thumb and fingers.



Textured Comfort Ergo Handles

Locking Pawl

Bolt Cutting

Extended

Extended Textured Ergo Handles



- Thumb Valley Protection
- Pocket Locket Locking Hasp
- Shear Cut **Bolt Cutters**
- Santoprene[™]
- Ergo Handles

#45-900's

45-915

45-918

Super T®-Stripper Wire Stripper

The industry standard for almost 50 years. Compact,

lightweight and easy to use. Features precision-ground,

knife-type blades, built-in looping holes, wire cutters

T®-Stripper Wire Stripper

and a convenient plier nose.

Traditional T®-Stripper Wire Stripper features with the added convenience of bolt-cutting holes and locking pawl. Curved comfort-grip handles accommodate high-volume wire stripping.



- Locking Pawl
- · Bolt Cutting
- Comfort
- Curved

and a comment pilot neces									•	Straight Handles		ranales								
	T®-\$																			
	6 a	3 10 0 12	0 12 2 14	14 16	16 18	18 20	20 22	22 24	24 26	26	28 30	30 32	Hole Size		#45-100's	#45-300's	#45-400's	#45-600's	#45-700's	
		T						22	24	26	28	30	Solid		45-125	45-317	45-417			
		T	T		Г		Г	24	26	28	30	32	Stranded	S TO STREET STREET	40-120	40-317	45-417	_		
		T	T	14	16	18			П	П	Γ		Solid	gi Bessense	45-121	45-316	45-416	45-616	45-716	
				16	18	20	22	24	26				Stranded	The Tanasa	45-121	45-510	45-410	45-010	40-710	
		10	12	14	16	18					Π		Solid	The second second	45-120		45-415		45-715	
		12	2 14	16	18	20					Γ		Stranded	hi harry	N. Harris	45-120		40-410	_	40-710
	8	3 10	12	14	16						Γ		Solid	A Charleston	_	45-315		45-615	_	
	1	0 12	2 14	16	18		Γ	Г	Γ		Γ		Stranded		_	40-010	_	43-013		
	6 8	3 10	12	14			Г		Γ		Γ		Solid		45-124	45-318	45-418	45-618	45-718	
	8 1	0 12	2 14	16	Г				Γ		Γ	Π	Strand							

45-123

Static Disp



T®-Stripper Wire Strippers

- Form-ground, knife-type blades for accurate, easy stripping without nicking insulation
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength



- Laser-etched wire gauge for easy-to-read visibility
- Spring-loaded automatic opening
- Corrosion-resistant, black oxide finish
- Tough steel construction

Description	Solid	Stranded	Cat. No.
T®-5 T®-Stripper Wire Stripper	10-18	12-20	45-120
T®-6 T®-Stripper Wire Stripper	14-24	16-26	45-121
T®-7 T®-Stripper Wire Stripper	22-30	24-32	45-125
T®-8 T®-Stripper Wire Stripper	6-14	8-16	45-124
T®-Stripper Wire Stripper – Metric	0.75-6mm²		45-120-341
T®-Stripper Wire Stripper – Metric	0.5-4	lmm²	45-125-341

NM Cable T®-Stripper Wire Strippers

- Easy, one-step stripping of outer jacket of NM cable - no slitting required
- Versatility to strip, cut and loop conductor wires with precision and ease
- Stripping holes for 12 or 14 AWG solid wire
- Locking pawl for safe storage

Description	Cat. No.
14/2 NM Cable T®-Stripper Wire Stripper	45-248
12/2 NM Cable T®-Stripper Wire Stripper	45-249
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	45-621
Reflex™ Super 12/3 & 14/3 Cable T®-Stripper Wire Stripper	45-622

NM Cable Dual-Hole T®-Stripper Wire Stripper

- Stripping holes for stripping two 12 AWG or two 14 AWG wires simultaneously
- Ability to strip both conductor wires of NM cable at one time

Description	Wire Range	Cat. No.
Premium T®-14 T®-Stripper Wire Stripper	12 or 14 AWG solid	45-247

Romex® is a registered trademark of Southwire.

Super T®-Stripper Wire Strippers

- 6-32 and 8-32 self-chasing screwcutting holes (not available on metric stripper)
- Curved, cushion-grip handles for ergonomic comfort
- Locking pawl to keep stripper in closed position
- Built-in wire cutter and looping holes
- Convenient plier nose for extra gripping strength
- Laser-etched wire gauge for easy-to-read visibility
- Spring-loaded automatic opening
- Tough steel construction, corrosion-resistant, black oxide finish

Description	Solid	Stranded	Cat. No.
Super T®-5 T®-Stripper Wire Stripper	8-16	10-18	45-315
Super T®-8 T®-Stripper Wire Stripper	6-14	8-16	45-318
Super T®-Stripper Wire Stripper – Metric	0.5-4mm ²		45-310-341
Super T®-Stripper Wire Stripper – Metric	0.75-	45-315-341	
Super T®-Stripper Wire Stripper – Metric	0.5-4mm²		45-317-341

Lil' Ripper Stripper™

- Rips Romex® outer jacket cleanly and
- Clips outer sheathing to remove excess Romex® jacket
- Strips inner conduit wires
- Looping holes loop wire for screw-on connections
- Twist-Assist™ tightens most popular sizes of winged twist-on connectors
- Injection molded elastomer grip provides a comfortable, slip resistant grip
- Strip length measuring scale allows for quick and easy measurements
- Conveniently fits in your pocket

Description	Cat. No.		
Lil' Ripper Stripper™	45-025		

Reflex™ Super T®-Stripper Wire Strippers

- 6/32 and 8/32 self-chasing screw-cutting holes
- Locking pawl for safe storage
- Ergonomic design for maximum comfort
- Curved handles reduce wrist fatigue
- Sleeves that extend to stripping head to cushion thumb and fingers
- Textured sleeves with extra cushioning for added comfort

Description	Solid	Stranded	Cat. No.
Reflex™ Super 12/2 & 14/2 NM Cable T®-Stripper Wire Stripper	12-2 and 14-2	_	45-621
Reflex™ Super 12/3 & 14/3 NM Cable T®-Stripper Wire Stripper	12-3 and 14-3	_	45-622