

# Bring control on Advanced Panels

Advanced Panels Magelis XBT GT/GK  
With control option



SoMachine



> 20 Magelis XBTGT/GK becomes HMI controllers

> Large display choice from 5"7 monochrome up to 15" color screen


> User-interface choice Touch or Keyboard

> Enhanced communication communication with Serial lines and Ethernet

> Advanced features like Video & Data management (data sharing / data logging)

# > SoMachine is the Schneider Electric single software package for machine automation

- ★ Configures HMI and control applications for Magelis XBT GT/GK as well as XBT GC and other PLCs and terminals.
- ★ Sets CANopen communication.
- ★ Includes Vijeo Designer, the preferred operator dialog configuration tool.
- ★ Offers advanced features (5 IEC languages, sharing of variables).
- ★ One common project file, simulation, single download, etc.



## > Magelis XBT GT/GK selection guide

### 5.7" monochrome touchscreen

Grey 16 levels, QVGA, 2 serial ports & 1 USB port	<b>XBTGT2110</b>
+ CF slot	<b>XBTGT2120</b>
+ Ethernet	<b>XBTGT2130</b>

### 5.7" colour touchscreen

4K colours QVGA, CF slot, 2 serial ports & 1 USB port	<b>XBTGT2220</b>
+ 65K colours & Ethernet	<b>XBTGT2330</b>
or + High Resolution VGA	<b>XBTGT2430</b>
+ High Brightness	<b>XBTGT2930</b>

### 7.5" colour touchscreen

4K colours VGA, CF slot, 2 serial ports & 1 USB port, Ethernet	<b>XBTGT4230</b>
+ 65K colours	<b>XBTGT4330</b>
+ 1 video port	<b>XBTGT4340</b>

### 10.4" colour touchscreen

4K colours VGA, CF slot, 2 serial ports & 1 USB port	<b>XBTGT5230</b>
+ 65K colours	<b>XBTGT5330</b>
or + 1 video port	<b>XBTGT5340</b>
+ High Resolution QVGA	<b>XBTGT5430</b>

### 12.1" colour touchscreen

65K colours QVGA, CF slot, 2 serial ports & 2 USB ports, Ethernet	<b>XBTGT6330</b>
+ 1 video port	<b>XBTGT6340</b>

### 15" colour touchscreen

65K colours XGA, CF slot, 2 serial ports, 2 USB ports, video ports & Ethernet	<b>XBTGT7340</b>
---	------------------

### 5.7" monochrome touchscreen & keyboard

Grey 16 levels, QVGA, CF slot, 2 serial ports, video ports, Ethernet & 1 USB port	<b>XBTGK2120</b>
---	------------------

### 5.7" colour touchscreen & keyboard

65K colours TFT, CF slot, 2 serial ports & 1 Ethernet port, built-in Ethernet TCP/IP	<b>XBTGK2330</b>
--	------------------

### 10.4" colour touchscreen & keyboard

65K colours VGA, CF slot, 2 serial ports, 2 USB ports & 1 Ethernet port, built-in Ethernet TCP/IP	<b>XBTGK5330</b>
---	------------------



**CANopen Master Module mandatory for Control function on XBTGT/GK**

**XBTZGCANM**

#### Schneider Electric Industries SAS

Head Office  
35, rue Joseph Monier - CS30323  
F92505 Rueil-Malmaison Cedex  
FRANCE

[www.schneider-electric.com](http://www.schneider-electric.com)

ART. 837577

Due to possible changes in standards and equipment, the features described in this document in the form of text and images are subject to confirmation by Schneider Electric.  
Publication: Schneider Electric  
Design: pemaco  
Printing: