

4-Port USB 2.0 Hi-Speed USB over Cat5 Hub with 3 local Ports and 1 Remote Port, TAA

MODEL NUMBER: U224-1R4-R



Description

Tripp Lite's U224-1R4-R is a kit that includes a 3-port USB 2.0 local transmitter unit, and a 1-Port USB 1.1 remote receiver unit. Connect up to 3 USB 2.0 devices to the local transmitter, while extending an additional USB 1.1 peripheral up to 150 ft. from your computer. Simply plug the transmitter into the USB port on your computer, connect your USB peripherals, and run Cat5e/Cat6 cable up to 150 ft. to the remote receiver unit and connected device. Plug-and-play; no software or drivers required. Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases.

Features

- Local transmitter unit features 3 USB 2.0 ports
- Remote receiver unit features 1 USB 1.1 port
- Locate a USB 1.1 peripheral up to 150 ft. from your computer
- Uses readily available Cat5e/Cat6 patch cable
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Specifications

OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A
PHYSICAL	
Color	Black

Highlights

- Local transmitter unit features 3 USB 2.0 ports
- Remote receiver unit features 1 USB 1.1 port
- Locate a USB 1.1 peripheral up to 150 ft. from your computer
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

Package Includes

- 3-port USB 2.0 local transmitter unit
- 1-port USB 1.1 remote receiver unit
- External Power Supply with NEMA 1-15P Plug (Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A)
- Owner's manual



Transmitter Unit Height (in.)	0.9
Transmitter Unit Width (in.)	2.4
Transmitter Unit Depth (in.)	3.3
Receiver Unit Height (in.)	0.9
Receiver Unit Width (in.)	1.8
Receiver Unit Depth (in.)	2.6
CONNECTIONS	
Ports	4
Side A - Connector 1	USB A (MALE)
Side A - Connector 2	RJ45 (FEMALE)
Side B - Connector 1	(4) USB A (FEMALE)
Side B - Connector 2	RJ45 (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>