

**Catalog Number:** TT-7-30-9-L  
**Product ID:** 7TAG054780R0022  
**UPC Number:** 72849414564  
**EAN Number:** 05415022000498  
**Status:** Active



Twist Tail Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 180mm (7.1 Inches), Width of 4.7mm (0.186 Inch), Thickness of 1.37mm (0.054 Inch), Tensile Strength Rating of 133 Newtons (30 Pounds), Maximum Bundle Diameter 44.45mm (1.75 Inches), 50 Pieces per Bag/20 Bags per Case

- Designed for quick, easy, tool-less installation. After installing, remove excess tail with a simple "bend, bend again and twist" motion.

Actual

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5037 Cable Ties & Wraps
Brand Name	Catamount
Type	Twist Tail Cable Tie
Special Features	Designed for quick, easy, tool-less installation. After installing, remove excess tail with a simple bend
Application	Bend again and twist "motion."
Width	0.186 Inch/4.7mm
Length	7.1 Inches/180mm
Thickness	0.054 Inch/1.37mm
Bundle Diameter	Max 1.75 Inches/44.45mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Plastic Pawl
Tensile Strength	30 Pounds/133 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	4.7mm
Length belt/tape/tie	180mm
Tie thickness	1.37mm
Max. bundle diameter	44.45mm
Min. holding force	133N
Operating temperature	85-85°C
Model	Internal tothing
Band closure	Plastic lip/-cam
Material	Plastic
Material quality	Polyamide PA
Halogen free	Y
Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
MIL approval	N
UL approval	Y

### Packaging

Inner Quantity	1
Inner Dimensions (inches)	11.5x5x.5
Outer Quantity	20
Outer Dimensions (inches)	10.4x9.1x4.8

Weight Uom

14.5 lbs. per 100

**Documents / Support Tools**

Technical Data Sheet Global

wsd-000536

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)