




brainboxes
www.brainboxes.com

Accessories - Cables

Cables

Brainboxes offers a variety of accessories that are compatible with various devices. Our products are supplied with everything you need to get started but you may require additional cables depending on your application.

All our cables are available to be purchased separately with no minimum order quantity. If you are unsure about any alternative cable requirements please speak to the sales team.



CC-095


LYNX CABLE 78 WAY D TO 8X25 PIN

Length = 1m

Packaged Weight = 0.877 kg, 1.93 pounds

Suitable for use with Brainboxes UC-275, PX-275 and CC-275: 8 x 25 pin RS232 cable, fully wired and moulded cable.

Comprised of one Male 78 pin D connector to octopus cables 1 metre long with 8 Male 25 pin D connectors.



CC-093

LYNX CABLE 78 WAY D TO 8X9 PIN


Length = 1m

Packaged Weight = 0.741 kg, 1.63 pounds

Suitable for use with Brainboxes UC-279, PX-279, and CC-279, 8 x 9 pin RS232 cable, fully wired and moulded cable.

Comprised of one Male 78 pin D connector to octopus cables 1 metre long with 8 Male 9 pin D connectors.

Accessories - Cables




CC-072

QUAD CABLE 37 WAY D TO 4X25 PIN

Length = 1m

Packaged Weight = 0.483 kg, 1.06 pounds

Suitable for use with Brainboxes UC-265: 4 x 25 pin RS232 cable, fully wired and moulded cable.
Comprised of one Male 37 pin D connector to quad cables 1 metre long with 4 Male 25 pin D connectors.



CC-060


QUAD CABLE 37 WAY D TO 4X9 PIN

Length = 1m

Packaged Weight = 0.383 kg, 0.84 pounds

Suitable for use with Brainboxes UC-268, UC-346 and UC-368: 4 x 9 pin RS232 cable, fully wired and moulded cable.

Comprised of one Male 37 pin D connector to quad cables 1 metre long with 4 Male 9 pin D connectors.



CC-213

QUAD CABLE 44 WAY D TO 4X9 PIN


Length = 1m

Packaged Weight = 0.362 kg, 0.80 pounds

Suitable for use with Brainboxes UC-701 and UC-260, 4 x 9 pin RS232 cable, fully wired and moulded cable.

Comprised of one Male 44 pin D connector to quad cables 1 metre long with 4 Male 9 pin D connectors.

Accessories - Cables




CC-191

DUO CABLE 44 WAY D TO 2X9 PIN D

Length = 0.05m

Packaged Weight = 0.171 kg, 0.38 pounds

Suitable for use with Brainboxes UC-253 and UC-734: 2 x 9 pin RS232 fully wired and moulded cables. Comprised of one DB44 pin connector with a 0.05 metre cable to 2 DB9 pin connectors.




CC-032

STD BRACKET LPT PRINTER FLYLEAD

Length = 0.30m

Packaged Weight = 0.042 kg, 0.09 pounds

Suitable for use with Brainboxes UC-257 (NB: this cable does not come as standard with UC-257). Comprised of one Female 25 pin D connector on a standard height bracket with 300mm long fly lead to an IDC 2x13, 26 way ribbon header.



CC-027

STD BRACKET 9 PIN SERIAL FLYLEAD


Length = 0.12m

Packaged Weight = 0.035 kg, 0.08 pounds

Suitable for use with Brainboxes UC-420, UC-101, UC-475 and PX-101, 1 x 9 pin adapter cable, fully wired and moulded cable.

Comprised of a Male 9 pin D connector on a standard height bracket with a 300mm long fly lead to an IDC 2x5, 10 way ribbon header.

Accessories - Cables




CC-224

QUAD CABLE 44 WAY D TO 4X25 PIN

Length = 1m

Packaged Weight = 0.353 kg, 0.78 pounds

Suitable for use with Brainboxes UC-271/UC-756: 4 x 25 pin RS232 cable, fully wired and moulded cable. Comprised of a Male 44 pin D connector to quad cables 1 metre long with 4 Male 25 pin D connectors.



US-045


USB TYPE A PLUG TO A RECEPTACLE 0.25M CABLE

Length = 0.25m

Packaged Weight = 0.035 kg, 0.08 pounds

Suitable for use with Brainboxes US-101 and US-324. Fully wired and moulded cable.

Comprised of a USB 2.0 Type A Male plug on a cable 250mm long to Type A Female receptacle.



VX-045

CABLE FOR VX-012/034


Length = 0.5m

Packaged Weight = 0.114 kg, 0.25 pounds

Suitable for use with Brainboxes VX-012 & VX-034: 2 Port 9 pin RS232 cable, fully wired and-moulded cable.

Comprised of a Female 26 pin D connector to duo cable 500mm long with 2 Male 9 pin D connectors.

Accessories - Cables



CC-401

LOW PROFILE 9 PIN SERIAL FLYLEAD


Length = 0.12m

Packaged Weight = 0.044 kg, 0.10 pounds

Suitable for use with Brainboxes PX-803, PX-801, UC-464, PX-203, PX-101, UC-203 AND UC-101.

Fully wired and moulded cable.

Comprised of a Male 9 pin D connector on a low profile bracket with a 120mm long fly lead to an IDC 2x5, 10 way ribbon header.



CC-412


LOW PROFILE LPT PRINTER PORT FLYLEAD

Length = 0.30m

Packaged Weight = 0.044 kg, 0.10 pounds

Suitable for use with Brainboxes UC-263, UC-203 and PX-203. Fully wired and moulded cable.

Comprised of a Female 25 pin D connector on a low profile bracket with 300mm long fly lead to an IDC 2x13, 26 way ribbon header.



US-063

USB TYPE A PLUG TO B PLUG CABLE

Length = 1m


Packaged Weight = 0.035 kg, 0.08 pounds

Suitable for use with Brainboxes US-346, US-279, US-842, US-257, US-313, US-601 and US-701.

Fully wired and moulded cable.

Comprised of a USB 2.0 Type A Male Plug on a cable 1000mm long to Type B Male Plug 1000mm.

Accessories - Cables



PM-031

PCMCIA 9 PIN CABLE

Length = 0.50m

Packaged Weight = 0.078 kg, 0.17 pounds

Suitable for use with Brainboxes PM-010/PM-020/
PM-120/PM-121, 9 pin RS232 cable fully wired and
moulded cable.

Comprised of a Slimline 15 way PCMCIA card
connector to 500mm cable with Male 9 pin D con-
nector.

Brainboxes can also supply custom cable options for specific applications and installations.

To discuss your individual requirements please contact our sales team:

Tel: +44 (0)151 220 2500
USA (Toll Free): +1 888 958 5538
Japan: +81-3-3833-2500

or e-mail: sales@brainboxes.com

Accessories - Cables

Check your cable selection for compatibility with Brainboxes product codes:

PART CODE	Comes as standard with:	Can also be used with:
CC-027	UC-420/UC-101/UC-475	
CC-032		UC-257
CC-060	UC-268/UC-346/UC-368	UC-265
CC-072	UC-265	UC-268/UC-346/UC-368
CC-093	UC-279/PX-279/CC-279	UC-275/PX-275/CC-275
CC-095	UC-275/PX-275/CC-275	UC-279/PX-279/CC-279
CC-191	UC-253/UC734	
CC-213	UC-701/UC-260	UC-271/UC-756
CC-224	UC-271/UC756	UC-701/UC-260
PM-031	PM-010/PM-020/PM-120/PM-121	
US-045	US-101/US-324	Can be used to extend any US range product
VX-045	VX-012/VX-034	
CC-401	PX-803/PX-801/UC-464/PX-203/PX-101/ UC-203/UC-101	
CC-412	UC-263/UC-203/PX-203	
US-063	US-346/US-279/US-842/US-257/US-313/ US-601/US-701	