












# UC-083

# uPCI 4xRS232 Opto Isolated TX RX GND CTS

### "SERIAL CARDS ENGINEERED TO EXCEED EXPECTATIONS"



**brain** boxes

#### Features

- 4 port RS232
- PCI 3.0
- 128 Byte Tx and 128 Byte Rx FIFOs
- Up to 921,600 Baud
- DB9 connector (9 Pin Male)
- Drivers for all popular operating systems
- Sample Programs, Test & Terminal software
- Lifetime Support
- Lifetime Warranty (registration required)

#### **Options**



uPCI 4xRS232 Opto Isolated TX RX GND CTS

#### Description

Universal PCI providing two RS232 serial ports with Opto Isolation on TX, RX, GND, CTS RTS lines. Data transfer rates up to 921,600 baud rates and the 128 byte deep transmit and 128 byte receive FIFOS, coupled with 1Mbit/s line drivers deliver uncompromising performance on your PC. Includes drivers for all Windows 32 bit and 64 bit Operating Systems, including Windows 7.

With Brainboxes industry renowned Lifetime Warranty and Lifetime Support!

#### Software

Microsoft signed drivers (easy installation & robust operation) for:

- Windows 7 32 bit 64 bit Editions
- Windows Server 2008 32 bit 64 bit Editions



- Windows Vista 32 bit 64 bit editions
- Windows Server 2003 32 bit 64 bit Editions

As well as: full product documentation, a thorough troubleshooting guide and terminal software. Detailed sample source code for many popular programming languages. Further OS support on next page.







ORDER

Description

uPCI 4xRS232 Opto Isolated TX RX GND CTS RTS

Code UC-083



# uPCI 4xRS232 Opto Isolated TX RX GND CTS

#### UC-083Full Specification

| Port  | Ports               | 4 x RS232  |
|---|---------------------|--|
| Pin 1 N.C. Pin 2 OPTO RXD Pin 3 OPTO TXD Pin 4 N.C. Pin 5 OPTO GND Pin 6 N.C. Pin 7 OPTO RTS Pin 8 OPTO CTS Pin 9 N.C.  Pin 6 Pin 9 | Connector           | DB9 Connector - 9 Pin Male   |
|   | FIFO size           | 128 RX FIFO + 128 TX FIFO  |
|   | Operating Distance  | EIA - RS232 Standard   |
|   | Cable               | 4 port cable 44 way D to 4x9 Pin   |
| Port Settings   | Baud Rate           | 921,600  |
| 921,600<br>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>>  | Data Bits           | 5,6,7 or 8   |
|   | Parity              | Odd, Even, None, Mark or Space   |
|   | Stop Bits           | 1, 1.5 or 2  |
|   | Flow Control        |  |
|   | Tx/Rx Modes         | Point to Point   |
| Interface PCI °   | OS Compatibility    | Microsoft Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit Editions Windows Vista 32 bit 64 bit Editions Windows Server 2003 32 bit 64 bit Editions Windows XP 32 bit 64 bit Editions Microsoft Windows 2000 DOS |
|   | BUS                 | PCI : Universal PCI is fully compatible with both 3.3Volt and 5Volt PCI slots.   |
| Approvals   | Industry Approvals  | AEO C-TPAT Microsoft Certified Gold Partner WEEE RoHS EMC: CE TAA  |
|   | Microsoft Approvals | Windows 7 32 bit 64 bit Editions Windows Server 2008 32 bit 64 bit editions Windows Vista 32 bit 64 bit editions Windows Server 2003 32 bit 64 bit editions Windows XP 32 bit 64 bit editions                                      |
| General   | PCB Layers          | 4  |
|   | Power Consumption   | 550mA @ 5V   |
|   | Weight              | 0.076 kg   |
|   | Size                | 134l x 18w x 120h mm   |
| Box Content   | Packaging           | Installation CD including manual, Microsoft signed drivers & utilities   |
|   | Card                | uPCI 4xRS232 Opto Isolated TX RX GND CTS RTS   |
|   |                     | 4 port cable 44 way D to 4x9 Pin   |
| Product Support   | Warranty            | Lifetime (online registration required)  |
|   | Support             | Lifetime Web, Email and Phone Support from fully qualified, friendly staff who work in and alongside the Product Development Team  |
| Additional  | OEM option          | Available for bulk buy OEM   |
| Elektra O5  | Made In             | Manufactured in the UK by Brainboxes Winner 2005 European Electronics Industry Awards "Manufacturer of the Year"   |
| WINNER Manufacturer of the Year Made in the UK  | Customisable        | Brainboxes operate a "Perfect Fit Custom Design" policy for volume users. More Info: sales@brainboxes.com  |

Other PCI Cards: 1xRS232 | 2xRS232 | 4xRS232 | 8xRS232 | 1xRS422/485 | 2xRS422/485 | 4xRS422/485 Other Brainboxes Ranges: PCI Express | Bluetooth Serial Adapter | Ethernet to Serial Adapter | PCMCIA Serial Card | ExpressCard Serial Adapter | USB to Serial