

## Economy Server Cabinet *DC200 Series*

Available while supplies last

**Note:** This product line has been discontinued as a stocked series. Information is for reference only. It has been replaced with **RB-DC Series**. For alternative solution assistance, please contact Hammond Customer Service - [sales@hammfg.com](mailto:sales@hammfg.com) or USA (716) 630-7030, Canada and International (519) 822-2960.



**RACK BASICS®**



### Features

- Constructed in 16-gauge steel.
- Two pairs of 19" EIA-310-D compliant square hole punched rails with rack unit markings.
  - Starter pack of M5 screws and cage nuts included.
  - For 10-32 hardware see the **1421CNABK Series**.
- Locking front door has attractive 4 point latch, curved and ribbed surface for added stability, and can be easily removed and hinged in either direction.
- Rear of cabinet features split locking doors making access easier in tight spaces.
- Pair of removable solid side panels include stiffeners for added strength.

### Specifications

- Includes two (2) 4" diameter cable entry holes (top) and one (1) 8" x 12" opening (bottom).
- Open frame bottom allows raised tile floor cable and air access.
- Bottom of cabinet includes:
  - Four (4) adjustable leveling feet
  - Four (4) recessed casters
- Rails can adjust in depth in 25mm increments.
- Grounding studs provided on frame.
- Finished in smooth black powder paint.
- Tested to nearly double the suggested load rating of 950 lbs..
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions.

### Gallery



### Accessories

- Universal Rack Shelf
- Rack Mount Locking Storage Drawer
- Sliding Keyboard Shelf
- Rack Unit Label
- Horizontal Lacing Strip
- Horizontal Hinged Cable Manager
- Cable Management Arm
- Rack Panels
- Adjustable Depth 4-Post Rack Mount Shelf
- Four Post Mounting Sliding Shelf
- Outlet Strips
- Adjustable Depth Cable Manager
- Horizontal Ring Cable Manager
- Horizontal Steel Finger Cable Manager
- Outlet Strips
- Mounting Hardware

Part No.	Overall Dimensions			Rack Units	Usable Mounting Dimensions			Shipping Weight
	Height	Width	Depth		Height	Width	Depth	
DC2004224	47.10	23.60	43.40	24U	42.00	19.00	38.00	280 lb
DC2004242	78.60	23.60	43.30	42U	73.50	19.00	38.00	385 lb

## DC200 Specific Accessories

Part No.	Description
DC2PBCLP	Accessory mounting bracket for Hammond vertical outlet strips and cable managers
DC200PR24	Pair of 24U Square Hole Mounting Rails
DC200PR42	Pair of 42U Square Hole Mounting Rails

## Compatible Vertical Cable Managers

Part No.	Description
C4VCM73BK1	Vertical Cable Manager with Hinged Door
VCT73	Vertical Cable Tray
VCTPDU73	Vertical Cable Tray with Toolless PDU Cutouts.

*Data subject to change without notice*