

**Rittal – The System.**

Faster – better – worldwide.

**► Catalog 33  
North American Edition 2012**

**500**

---

**Rittal. Power and Vision!**

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# EB hinge cover junction box

Depth: 5 - 6" (120 - 155 mm), Height: 10 - 16" (250 - 400 mm)

<b>Height</b> (H1) inches (mm)	PU	12 (300)	16 (400)	16 (400)	10 (250)	12 (300)	Page
<b>Width</b> (B1) inches (mm)		12 (300)	8 (200)	12 (300)	8 (200)	10 (250)	
<b>Depth</b> (T1) inches (mm)		5 (120)	5 (120)	5 (120)	6 (155)	6 (155)	
Panel height (G1) inches (mm)		11 (285)	15 (385)	15 (385)	9 (235)	11 (285)	
Panel width (F1) inches (mm)		11 (275)	7 (175)	11 (275)	7 (175)	9 (225)	
<b>Part No.</b>	1	<b>1555.500</b>	<b>1550.500</b>	<b>1556.500</b>	<b>1752.500</b>	<b>1753.500</b>	
Weight lb (kg)		11 (5.0)	11 (5.0)	14 (6.4)	8 (3.6)	11 (5.0)	

## Accessories

Wallmount bracket	4			1590.000			628
Handle	1			2533.000			606

Depth: 6" (155 mm), Height: 14 - 32" (350 - 800 mm)

<b>Height</b> (H1) inches (mm)	PU	14 (350)	16 (400)	16 (400)	24 (600)	32 (800)	Page
<b>Width</b> (B1) inches (mm)		12 (300)	12 (300)	14 (350)	12 (300)	12 (300)	
<b>Depth</b> (T1) inches (mm)		6 (155)	6 (155)	6 (155)	6 (155)	6 (155)	
Panel height (G1) inches (mm)		13 (335)	15 (385)	15 (385)	23 (585)	31 (785)	
Panel width (F1) inches (mm)		11 (275)	11 (275)	13 (325)	11 (275)	11 (275)	
<b>Part No.</b>	1	<b>1754.500</b>	<b>1577.500</b>	<b>1755.500</b>	<b>1578.500</b>	<b>1579.500</b>	
Weight lb (kg)		13 (5.8)	16 (7.1)	14 (6.3)	23 (10.4)	29 (13.2)	

## Accessories

Wallmount bracket	4			1590.000			628
Handle	1			2533.000			606