

Print Ribbons

“Drop & Click” print ribbons for quick and easy supply changes.

- Tough, smear-proof ribbons that produce long-lasting printed text
- Print can withstand years in industrial areas and outdoor conditions
- Ribbons ship in self-contained cartridges that drop straight into printer with a “click”
- No calibrating, no threading, no wasted feeding, no hassles, and the ink will always be facing the right direction!
- Printer notifies user if installed ribbon is not recommended for installed labels



Installs in 3 seconds and the ink always faces the right direction!

BBP®33 Print Ribbons

Catalog #	Color	Size
Heavy-duty ribbons for outdoor & harsh facility materials:		
B30-R10000	Black	4.330" x 200'
B30-R10000-WT	White	4.330" x 200'
B30-R10000-RD	Red	4.330" x 200'
B30-R10000-GN	Green	4.330" x 200'
B30-R10000-BL	Blue	4.330" x 200'
B30-R10000-YL	Yellow	4.330" x 200'
B30-R10000-OR	Orange	4.330" x 200'
B30-R10000-MA	Magenta	4.330" x 200'

NOTE: * B30-R4500-SV ribbon for use with B-342 black PermaSleeves® only.

Catalog #	Color	Size
Industrial grade print ribbons:		
B30-R4300	Black	4.330" x 200'
B30-R6000	Black	4.330" x 200'
B30-R6200	Black	4.330" x 200'
B30-R6400	Black	4.330" x 200'
B30-R6600	Black	4.330" x 200'
B30-R4400-WT	White	4.330" x 200'
B30-R4500-SV	Silver*	4.330" x 200'



BBP®33 Print Ribbon / Material Compatibility (Updated March 2013)

Update your BBP®33 printer firmware. Recommendations below assume current firmware version. Visit www.BradyID.com/bbp33 for free upgrade via download.

B-#	Material	B30-R4300 (Black)	B30-R6000 (Black)	B30-R6200 (Black)	B30-R6400 (Black)	B30-R6600 (Black)	B30-R10000 (Black)	B30-R4400-WT (White)	B30-R10000-WT (White)	B30-R4500-SV (Silver)	B30-R10000 (Colors)
B-342	PermaSleeve® PS Marker	●	—	—	—	●	—	—	—	●*	—
B-345	PermaSleeve® HT Marker	—	●	—	—	●	—	●*	—	—	—
B-423	Glossy White Polyester	—	●	●	—	—	—	—	—	—	—
B-424	Matte White Paper	●	—	—	—	—	—	—	—	—	—
B-425	Matte White Polypropylene	●	—	—	●	—	—	—	—	—	—
B-426	Matte Amber Polyimide	●	—	—	—	—	—	—	—	—	—
B-427	Vinyl Self-Laminating	●	—	—	—	—	—	—	—	—	—
B-428	Metallized Polyester	●	—	—	—	—	—	—	—	—	—
B-430	Glossy Clear Polyester	—	●	●	—	—	—	●	—	—	—
B-432	Glossy Clear Polyester	—	●	—	—	—	—	●	—	—	—
B-434	Gloss Metallized Polyester	—	●	—	—	—	—	—	—	—	—
B-438	Tamper Evident Metallized Polyester	●	—	—	—	—	—	—	—	—	—
B-457	Glossy White Polyimide	—	●	—	—	—	—	—	—	—	—
B-477	Glossy White Static Dissipative Polyimide	—	●	—	—	—	—	—	—	—	—
B-478	Glossy White Low Profile Static Dissipative Polyimide	—	●	—	—	—	—	—	—	—	—
B-479	Matte White Low Profile Static Dissipative Polyimide	—	●	—	—	—	—	—	—	—	—
B-483	Glossy White Polyester	—	●	—	—	—	—	—	—	—	—
B-486	Matte Metallized Polyester	●	—	—	—	—	—	—	—	—	—
B-489	Matte White Polyester	●	—	—	—	—	—	—	—	—	—
B-498	Repositionable Coated Vinyl Cloth	●	—	●	—	—	—	—	—	—	—
B-499	Coated Nylon Cloth	—	●	—	—	—	—	—	—	—	—
B-509	Printable Magnetic	—	●	—	—	—	●	—	—	—	●**
B-526	Photoluminescent Polyester	—	●	—	—	—	●	—	—	—	●**
B-549	Cold Temp Polyester	—	●	—	—	—	●	—	●	—	●**
B-551	Non-Adhesive Tag	—	●	—	—	—	●	—	—	—	●**
B-569	Low-Halide Polyester	—	●	—	—	—	●	—	●	—	●**
B-581	Repositionable Vinyl	—	●	—	—	—	●	—	●	—	●**
B-584	Retro Reflective	—	●	—	—	—	●	—	—	—	●**
B-593	Raised Panel Engraved Plate Substitute	—	●	—	—	—	—	●	—	—	—
B-595	Outdoor Vinyl	—	●	—	—	—	●	—	●	—	●**
B-7642	PermaSleeve® HX Marker	●	—	—	●	—	—	—	—	—	—

Refer to the corresponding Tech Data Sheets for complete material information at www.BradyID.com/techdata.

*B30-R4500-SV ribbon for use with B-342 black PermaSleeves® only; B30-R4400-WT ribbon for use with B-345 black PermaSleeves® only.

**Colored ribbons optimized for use on white material. Test use on other material colors for suitability to your application.