








Stop Switches (Assembled), continued

Non-Illuminated Stop Switches

	Style	Contacts	Part Number
Ø 40mm Pushlock Turn Reset*		1NO	AVW410-R*
		1NC	AVW401-R*
		1NO-1NC	AVW411-R*
		2NO	AVW420-R*
		2NC	AVW402-R*
Ø 29mm Pushlock Turn Reset*		1NO	AVW310-R*
		1NC	AVW301-R*
		1NO-1NC	AVW311-R*
		2NO	AVW320-R*
		2NC	AVW302-R*
Ø 40mm Push-Pull		1NO	AYW410-⊙
		1NC	AYW401-⊙
		1NO-1NC	AYW411-⊙
		2NO	AYW420-⊙
		2NC	AYW402-⊙
Ø 40mm Pushlock Key Reset *		1NO	AXW410- R*
		1NC	AXW401- R*
		1NO-1NC	AXW411- R*
		2NO	AXW420- R*
		2NC	AXW402- R*

- 1. *Available in Red only.
- 2. In place of ⊙, specify the Button Color Code from table.
- 3. For sub-assembled part numbers, see next page.
- 4. For accessories, see page 677.
- 5. For dimensions, see page 679.

Illuminated Stop Switches

	Style	Type	Contacts	Part Number
Ø 40mm Pushlock Turn Reset Type		Transformer	1NO-1NC	AVLW4 ⊕ 11 ⊕ -R*
			2NO	AVLW4 ⊕ 20 ⊕ -R*
			2NC	AVLW4 ⊕ 02 ⊕ -R*
		Full Voltage	1NO-1NC	AVLW49911 ⊕ -R* - ⊕
		2NO	AVLW49920 ⊕ -R* - ⊕	
		2NC	AVLW49902 ⊕ -R* - ⊕	
Ø 29mm Pushlock Turn Reset		Transformer	1NO-1NC	AVLW3 ⊕ 11 ⊕ -R*
			2NO	AVLW3 ⊕ 20 ⊕ -R*
			2NC	AVLW3 ⊕ 02 ⊕ -R*
		Full Voltage	1NO-1NC	AVLW39911 ⊕ -R* - ⊕
		2NO	AVLW39920 ⊕ -R* - ⊕	
		2NC	AVLW39902 ⊕ -R* - ⊕	
Ø 40mm Push-Pull		Transformer	1NO-1NC	AYLW4 ⊕ 11 ⊕ -⊙
			2NO	AYLW4 ⊕ 20 ⊕ -⊙
			2NC	AYLW4 ⊕ 02 ⊕ -⊙
		Full Voltage	1NO-1NC	AYLW49911 ⊕ -⊙ - ⊕
		2NO	AYLW49920 ⊕ -⊙ - ⊕	
		2NC	AYLW49902 ⊕ -⊙ - ⊕	

- 1. *Available in red only.
- 2. In place of ⊕, specify the Lens Color Code (see table above).
- 3. In place of ⊕, specify the Full Voltage Code (lamp voltage) (see table above).
- 4. In place of ⊕, specify the Transformer Voltage Code (see table above).
- 5. In place of ⊕, specify the Lamp Type Code from table above.
- 6. For sub-assembly part numbers, see next page.
- 7. For accessories, see page 677.
- 8. For dimensions, see page 679.

① Button Color Codes

Color	Code
Black	B
Green	G
Red	R
Blue	S
White	W
Yellow	Y

② LED/Lens Color Codes


Color	Code
Amber	A
Green	G
Red	R
Blue	S
White	W

③ Full Voltage Codes

Voltage	Code
6V AC/DC	6V
12V AC/DC	12V
24V AC/DC	24V
120V AC	120V (LED only)
240V AC	240V (LED only)

④ Transformer Voltage Codes

Voltage	Code
120VAC	126
240VAC	246
480VAC	486

 Transformers step down to 6V.

⑤ Lamp Type Codes

Lamp	Code
Incandescent	Blank
LED	D