

DIAZED FUSE LINK 500V F.CABLE AND LINE PROTECTION OP.CL.GL,SZ.DII,THREAD E27,4A



Figure similar

Model		
product brand name		SENTRON
Product designation		DIAZED fuse
Design of the product		For cable and line protection
Design of the fuse link		DIAZED fuse link
General technical data		
Tripping characteristic class		Other
Size of fuse system / acc. to DIN EN 60269-1		DII
Operating class of the fuse link		gG
circuit-breaker / Design		5SB2
Supply voltage		
• at AC / Rated value	V	500
• at DC	V	500
Protection class		
Protection class IP		IP20, with connected conductors
Switching capacity		
Switching capacity current		
• at DC / acc. to IEC 60947-2 / Rated value	kA	8

- acc. to IEC 60947-2 / Rated value

kA	50
----	----

Dissipation

Active power loss		
<ul style="list-style-type: none"> • for rated value of the current / at AC / in hot operating state / per pole 	W	2

Electricity

rated current I _n / IEC, DIN/VDE / at 40 Cel	A	3.8
Current / at AC / Rated value	A	4

Appearance

Color coding of the fuse link		brown
--------------------------------------	--	-------

Product details

Product description		Using screw adapter or adapter sleeves
----------------------------	--	--

Mechanical Design

mounting position		Any, preferably vertical
Net weight	g	27

Environmental conditions

Ambient temperature		
<ul style="list-style-type: none"> • minimum • maximum • during storage / Note 	°C	-5 40 Air humidity 90% at 20 °C
Environmental category		Up to 45°C at 95 % rel. humidity
Equipment marking		
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 		F F

General Product Approval	Declaration of Conformity	Test Certificates
---------------------------------	----------------------------------	--------------------------



[Typprüfbescheinigung/Werkszeugnis](#)

Test Certificates	Shipping Approval	other
--------------------------	--------------------------	--------------

[spezielle Prüfbescheinigung](#)



[Umweltbestätigung](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SB221>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/5SB221/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SB221

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

24.07.2015