



Item	Capacitance [pF]	TCC	Tolerance	Voltage	Part Number	Kit Part Number	Pcs.
1	1,0	HIFREQ	±0.10pF	250	VJ0603D1R0BXPAPJ	VJ0603HIFRQ1KIT	15 pcs. each value
2	1,2	HIFREQ	±0.10pF	250	VJ0603D1R2BXPAPJ		
3	1,5	HIFREQ	±0.10pF	250	VJ0603D1R5BXPAPJ		
4	1,8	HIFREQ	±0.10pF	250	VJ0603D1R8BXPAPJ		
5	2,0	HIFREQ	±0.10pF	250	VJ0603D2R0BXPAPJ		
6	2,2	HIFREQ	±0.10pF	250	VJ0603D2R2BXPAPJ		
7	2,4	HIFREQ	±0.10pF	250	VJ0603D2R4BXPAPJ		
8	2,7	HIFREQ	±0.10pF	250	VJ0603D2R7BXPAPJ		
9	3,0	HIFREQ	±0.10pF	250	VJ0603D3R0BXPAPJ		
10	3,3	HIFREQ	±0.10pF	250	VJ0603D3R3BXPAPJ		
11	3,9	HIFREQ	±0.25pF	250	VJ0603D3R9CXPAPJ		
12	4,7	HIFREQ	±0.25pF	250	VJ0603D4R7CXPAPJ		
13	5,6	HIFREQ	±0.25pF	250	VJ0603D5R6CXPAPJ		
14	6,8	HIFREQ	±0.25pF	250	VJ0603D6R8CXPAPJ		
15	8,2	HIFREQ	±0.25pF	250	VJ0603D8R2CXPAPJ		
16	10	HIFREQ	+5%	250	VJ0603D100JXPAPJ		
17	12	HIFREQ	+5%	250	VJ0603D120JXPAPJ		
18	15	HIFREQ	+5%	250	VJ0603D150JXPAPJ		
19	18	HIFREQ	+5%	250	VJ0603D180JXPAPJ		
20	20	HIFREQ	+5%	250	VJ0603D200JXPAPJ		
21	22	HIFREQ	+5%	250	VJ0603D220JXPAPJ		
22	27	HIFREQ	+5%	250	VJ0603D270JXPAPJ		
23	30	HIFREQ	+5%	250	VJ0603D300JXPAPJ		
24	33	HIFREQ	+5%	250	VJ0603D330JXPAPJ		
25	39	HIFREQ	+5%	250	VJ0603D390JXPAPJ		
26	47	HIFREQ	+5%	250	VJ0603D470JXPAPJ		