Flexible LED Strip Accessories

	NTE Type No.	Description	
	, , ,	Power Supplies and Dimmers	
8	LEDTA-6	Power Supply, 12V, 2A, 24W, 2.1mm x 5.5mm plug	
*	69-D24	Power Supply, 12V, 2A, 24W, 2.1mm x 5.5mm plug	
	69-D36	Power Supply, 12V, 3A, 36W, 2.1mm x 5.5mm plug	
	69-D48	Power Supply, 12V, 4A, 48W, 2.1mm x 5.5mm plug	
	69-D72	Power Supply, 12V, 6A, 72W, 2.1mm x 5.5mm plug	
	69-DIM1	LED Dimmer, RF, Remote Controlled, 12V, 8A, 96W for Single Color LED Strips. For use with up to four 24 watt, two 36 watt, two 48 watt, or one 72 watt LED Strip(s). Contains 1 remote and 1 dimmer.	
6	69-DIM2	LED Dimmer, Knob Operated Control, 12V, 8A, 96W for Single Color LED Strips. For use with up to four 24 watt, two 36 watt, two 48 watt, or one 72 watt LED Strip(s).	
Remote Controls			
	69-RTC1	Remote Control and Receiver for Red/Green/Blue flexible LED strips. Soft touch solid gradual hopping modes color ring. Contains 1 remote and 1 receiver.	
		Connectors	
	69-A1	Female DC Connector with 5.75 inch leads, 5.5mm x 2.1mm for power supplies and remote receiver	
	69-A2	3528 Size LED Connector with 5.75 inch leads – Add to cut strips * For 300 LEDs per Reel ONLY	
	69-A3	5050 Size LED Solid Color Connector with 5.75 inch leads – Add to cut strips	
	69-A4	5050 Size LED Red/Green/Blue Connector with 5.75 inch leads – Add to cut strips	
1	69-A5	3528 Size LED Solid Color Connector – For joining strips * For 300 LEDs per Reel ONLY	
(69-A6	5050 Size LED Solid Color Connector – For joining strips	
6	69-A7	5050 Size LED Red/Green/Blue Connector – For joining strips	
	69-A8	Waterproof 3528 and 5050 Size LED Solid Color Connector	
	69-A9	Waterproof DC Connectors (Male and Female) for power supplies and remote receiver	
	69-A10	Waterproof 5050 Size LED Red/Green/Blue Connector	

Flexible LED Strip Accessories (Cont'd)

	NTE Type No.	Description	
Connectors (Cont'd)			
600	69-A11	3528 Size LED L Connector – For joining strips * For 300 LEDs per Reel ONLY	
Q.	69-A12	5050 Size LED L Connector – For joining strips	
	69-A13	5050 Size LED Red/Green/Blue L Connector – For joining strips	
de la companya dela companya dela companya dela companya de la companya de la companya de la companya dela companya de la companya de la companya dela company	69-A14	3528 Size LED T Connector – For joining strips * For 300 LEDs per Reel ONLY	
I.E.	69-A15	5050 Size LED T Connector – For joining strips	
The same of the sa	69-A16	5050 Size LED Red/Green/Blue T Connector – For joining strips	
	69-A17	Female DC Connector with 2 ft. leads, 5.5mm x 2.1mm for power supplies and remote receiver	
	69-A18	Female DC Connector with 5 ft. leads, 5.5mm x 2.1mm for power supplies and remote receiver	
	69-A19	Female DC Connector with 10 ft. leads, 5.5mm x 2.1mm for power supplies and remote receiver	