



# Product Catalog

for professionals

[Products](#) > 15836

## 15836 – FLE26HT3/2/827

GE Soft White Spiral® T3 - Facilities; Retail Display; Hospitality; Office; Restaurant

Print this Page

Convert to PDF

**This product is no longer manufactured.**

• Up to 75% energy savings One piece unit screws directly into incandescent sockets T3 Spirals® lamps provide economical solution with small overall size

• Long life -8000-12,000 hour rating

a product of  
**ecomagination**




High Color Rendering  
cUL Listed  
Energy Savings  
 UL Listed



Bulb



Base



Package



[View Larger](#)

### GENERAL CHARACTERISTICS

Lamp type	Compact Fluorescent - Self-Ballasted
Bulb	T3
Base	Medium Screw (E26)
ENERGY STAR® Qualified	Yes
Primary Application	Standard; Facilities; Retail Display; Hospitality; Office; Restaurant
Equivalent Wattage (NOM)	100 W
Rated Life (NOM)	10000 hrs
Starting Temperature (MIN)	-15 °C(5 °F)
Total Harmonic Distortion (THD) (NOM)	120 %
Mercury Content (NOM)	4 mg
Picograms of Mercury (NOM)	313 picograms Hg per mean lumen hour
<ul style="list-style-type: none"> <li>Contains Mercury, For more on clean up and safe disposal visit <a href="http://epa.gov/cfl">epa.gov/cfl</a></li> </ul>	

### PHOTOMETRIC CHARACTERISTICS

Initial Lumens (NOM)	1750
Mean Lumens (NOM)	1400
Nominal Initial Lumens per Watt (NOM)	67
Color Temperature (NOM)	2700 K
Color Rendering Index (CRI) (NOM)	82

### ELECTRICAL CHARACTERISTICS

### ADDITIONAL RESOURCES

[Disposal Policies & Recycling Information](#)

### YOU MIGHT ALSO BE INTERESTED IN...

#### For Longer Life



[GE Soft White Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant](#)  
Product code: 46270

• Up to 75% energy savings One piece unit screws directly into incandescent sockets

• Super long life

[COMPARE](#)

#### For Energy



[GE Soft White Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant](#)  
Product code: 46270

• Up to 75% energy savings One piece unit screws directly into incandescent sockets

• Super long life

[COMPARE](#)

#### For Better Light



[GE Soft White Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant](#)  
Product code: 46270

• Up to 75% energy savings One piece unit screws directly into incandescent sockets

10/13/2014

Lighting | FLE26HT3/2/827 | 15836 | GE Lighting

Wattage (NOM)	26.0
Voltage (NOM)	120.0
Input Voltage (NOM)	120.0 V
Input Current (NOM)	0.39 A
Power Factor (NOM)	0.6

#### DIMENSIONS

Maximum Overall Length (MOL) (NOM)	5.2000 in (132.0 mm)
Nominal Length (NOM)	5.1000 in (129.5 mm)

#### PRODUCT INFORMATION

Product Code	15836
Description	FLE26HT3/2/827
Standard Package	Case
Standard Package GTIN	10043168158364
Standard Package Quantity	10
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168158367

#### ⚠ CAUTIONS & WARNINGS

-

[See list of cautions & warnings.](#)

#### NOTES

- Best performance if operated base up and at 77 degrees F (25C) ambient temperature.
- Fluorescent lamp lumens decline during life
- Lumens on one piece self ballasted lamp systems are measured base up.
- Most one piece self ballasted lamps for incandescent sockets and plug-in lamps with screw-in adapters do not work with clip-on shades
- Use only on 120V 60 Hz circuits. Do not use on dimming circuits, photocells or timers. Do not use in wet locations.

- Super long life

[COMPARE](#)

#### For Safety



[GE Soft White Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant](#)  
Product code: 46270

- Up to 75% energy savings One piece unit screws directly into incandescent sockets

- Super long life

[COMPARE](#)

#### For Super Long Life



[GE Soft White Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant](#)  
Product code: 46270

- Up to 75% energy savings One piece unit screws directly into incandescent sockets

- Super long life

[COMPARE](#)

#### For Environmental



[GE Soft White Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant](#)  
Product code: 46270

- Up to 75% energy savings One piece unit screws directly into incandescent sockets

- Super long life

[COMPARE](#)

\*Click on product for more specification details

[Return To Top](#)