

CIRCULAR POWER CONNECTORS



PRODUCT DRAWING
 English
 3D PDF

TE CONNECTIVITY (TE) 23-37 RCPT HSG,REV SEX,CPC

213864-1 TE Internal Number: 213864-1

Always EU RoHS/ELV Compliant

Product Type Housing Number of Positions 37 Applies To Panel Housing Type Receptacle Reverse Gender Reverse

Product Drawings	RECEPTACLE HOUSING, REVERSE SEX, SIZE 23, CPC PDF English
CAD Files	3D PDF PDF 3D
	Customer View Model 2D_DXF.ZIP English
	Customer View Model 3D_IGS.ZIP English
	Customer View Model 3D_STP.ZIP English
Catalog Pages/Data Sheets	AMP Circular Connectors For Commercial Signal & Power Applications PDF English
Product Specifications	
Application Specification	Circular Plastic Connectors (CPC) PDF English

Please review product documents or **contact us** for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

 Product Type Features
 Product Type
 Housing

 Housing Type
 Receptacle

y D f v

	Contact Type	JULKEL	
Configuration Features	Number of Positions	37	
	Reverse Gender	Reverse	
	Number of Power Positions	0	
	Number of Signal Positions	37	
	Keying	В	
Body Features	Thread Size	1-3/8 - 18 UNEF-2A	
Contact Features	Contact Protection	With	
Mechanical Attachment	Mating Alignment	With	
	Mating Retention	With	
	Panel Mount Retention Type	Flange with Mounting Holes	
	Mating Retention Type	Threaded Coupling	
	Mating Alignment Type	Keyed	
Housing Features	Housing Color	Black	
	Shell Type	All Plastic	
	Housing Material	Nylon - GF	
	Shell Size	23	
	UL Flammability Rating	UL 94V-0	
	Body Orientation	Straight	
Dimensions	Accepts Wire Insulation Diameter Range	2.54 mm [.1 in]	
Usage Conditions	Sealed Condition	Not Sealed	
	Fluid Resistance	None	
Operation/Application	Applies To	Panel	
Identification Marking	Reverse Numbering	With	
Industry Standards	VDE Tested	No	
Packaging Features	Packaging Method	Package	

	Packaging Quantity	1
Other	Comment	4 Locating Key Arrangement.
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	

CUSTOMERS ALSO BOUGHT

CIRCULAR POWER CONNECTORS	STANDARD POWER RELAYS	CIRCULAR POWER CONNECTORS	POWER CONTACTS
			THIN
CPC PLUG ASSEMBLY SIZE 23-37 213850-1	R10S-E1Y4-J1.0K=R10 R10S-E1Y4-J1.0K	23-37 RCPT HSG, STD SEX, CPC 213860-1	III+ SKT, 18-16, 30AU/FL, STRIP 66100-9
Save to List	Save to List	Save to List	Save to List
•			1
Relation Type	•		NI Compare 0/10 ↔
RELATIONSHIP Mating Products Jsed to identify Mating Parts			See All Mating Products
	PRODUCT - MATING PRODUCTS Connectors - Circular Power Conn AMP CPC	ectors Always EU RoHS/EL	V Compliant
	CPC PLUG ASSEM SIZE 23-37 - 21385	51	-
	TE INTERNAL NUMBER: 213850-1	Connector System N	
		Housing Type Plug Reverse Gender Re	verse