Trim Trio #16 contacts

SOURIAU



Stamped and formed contacts with selective plating

A unique contact technology which provides cost containment benefits without sacrificing performance.

Gold over nickel plating only on active area	√	Less sensitive to gold price
No impact to electrical performance	√	Exceptional contact performance maintained
Selective plating is available for both female and male contacts from wire size 30 AWG to 14 AWG	√	A full contact range
Available on a reel	1	Suitable for automatic crimping



Trim Trio #16 contacts

Technical features

• S18


- area 1: 0.76 $\mu_{\rm m}$ minimum of gold over nickel
- area 3: 1.3 μ_m minimum of tin over nickel
- area 4: 1.3 μ_m minimum of nickel


• S31

- area 1: gold flash over nickel

Ordering information

- area 3: 1.3 μ_{m} minimum of tin over nickel
- area 4: 1.3 $\mu_{\rm m}^{\rm m}$ minimum of nickel







Actual reference	New equivalent proposed part number	Actual reference	New equivalent proposed part number
SC14M1S6	SC14M1S18	SC14M1D70	SC14M1S31
SC14ML1S6	SC14ML1S18	SC14ML1D70	SC14ML1S31
SC16M11S6	SC16M11S18	SC16M11D70	SC16M11S31
SC16M1S6	SC16M1S18	SC16M1D70	SC16M1S31
SC16ML11S6	SC16ML11S18	SC16ML11D70	SC16ML11S31
SC16ML1S6	SC16ML1S18	SC16ML1D70	SC16ML1S31
SC20M1S6	SC20M1S18	SC20M1D70	SC20M1S31
SC20ML1S6	SC20ML1S18	SC20ML1D70	SC20ML1S31
SC24M1S6	SC24M1S18	SC24M1D70	SC24M1S31
SC24ML1S6	SC24ML1S18	SC24ML1D70	SC24ML1S31
SM14M1S6	SM14M1S18	SM14M1D70	SM14M1S31
SM14ML1S6	SM14ML1S18	SM14ML1D70	SM14ML1S31
SM16M11S6	SM16M11S18	SM16M11D70	SM16M11S31
SM16M1S6	SM16M1S18	SM16M1D70	SM16M1S31
SM16ML11S6	SM16ML11S18	SM16ML11D70	SM16ML11S31
SM16ML1S6	SM16ML1S18	SM16ML1D70	SM16ML1S31
SM20M1S6	SM20M1S18	SM20M1D70	SM20M1S31
SM20ML1S6	SM20ML1S18	SM20ML1D70	SM20ML1S31
SM24M1S6	SM24M1S18	SM24M1D70	SM24M1S31
SM24ML1S6	SM24ML1S18	SM24ML1D70	SM24ML1S31



For further information, visit our website www.souriau-industrial.com or contact us at contactindustry@souriau.com