

## Keyspan Mini DisplayPort to HDMI Adapter, Video Converter for Mac/PC, 1920x1200/1080p (M/F) 6-in.

MODEL NUMBER: **P137-06N-HDMI**



### Description

Tripp Lite's P137-06N-HDMI, Mini DisplayPort Male to HDMI Female adapter allows you to connect a Mac or PC with a Mini DisplayPort or Thunderbolt™ output to a HDMI monitor.

Ideal for Thunderbolt™ /Mini DisplayPort equipped laptops, Chromebooks, MacBooks, and Microsoft Surface. Mac 10.11, Windows 10 Compatible.

Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p. Fully molded ends ensure long life enjoyment.

The P137-06N-HDMI is a Passive adapter, and requires that the connected computer has a DP++ ( DisplayPort ++ ) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini DisplayPort source for compatibility.

### Features

- Connect a HDMI monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- HDCP compliant
- The P137-06N-HDMI supports transmission of an audio signal as long as it is supported by the Mini Displayport source. Check the documentation for your Mini Displayport source for compatibility.
- The P137-06N-HDMI is a Passive adapter, and requires that the connected computer has a DP++ (

### Highlights

- Connect a HDMI monitor to a Mac or PC with a Mini Displayport output
- Compatible with the Thunderbolt port on Mac computers
- Plug-and-play convenience—no drivers or software needed
- Supports computer video resolutions up to 1920 x 1200, and HD resolutions up to 1080p
- HDCP compliant
- This product is a passive adapter and requires that the connected computer has a DP++ (DisplayPort ++ ) dual-mode port

### System Requirements

- Mac or PC with a Mini Displayport port; Compatible with the Thunderbolt port on Mac computers
- Monitor with a HDMI port
- The P137-06N-HDMI supports transmission of an audio signal as long as it is supported by the Mini Displayport source. Check the documentation for your Mini Displayport source for compatibility.
- The P137-06N-HDMI is a Passive adapter, and requires that the connected computer has a DP++ ( Displayport ++ ) port, which allows HDMI and DVI signals to be passed



DisplayPort ++ ) port, which allows HDMI and DVI signals to be passed through; check the documentation for your Mini Displayport source for compatibility.

through; check the documentation for your Mini Displayport source for compatibility.

- Not for use with MST Hubs. For compatibility with MST Hubs, use a Displayport 1.2 compliant product such as P137-06N-HD-UHD

#### Package Includes

- Keyspan by Tripp Lite P137-06N-HDMI Mini Displayport to HDMI Adapter

## Specifications

MODEL TEXT	
Key Benefit	Connect a HDMI monitor to a Mac or PC with a Mini Displayport output
INPUT	
Cable Length (in.)	6
Cable Length (cm)	15.24
PHYSICAL	
Color	White
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<https://www.tripplite.com/products/product-certification-agencies>