

USB 3.0 SuperSpeed to Dual SATA External Hard Drive Docking Station with Cloning for 2.5 in./3.5 in. HDD

MODEL NUMBER: **U339-002**



Description

Tripp Lites U339-002 USB 3.0 SuperSpeed to Dual SATA External Hard Drive Docking Station allows two SATA 2.5in or 3.5in hard drives (HDD) or solid state drives (SSD) to be connected simultaneously to a computer through USB. Supports 3.5" drives up to 4TB. Off-line cloning allows hard drive duplication without being connected to a computer.

Utilizing SuperSpeed USB 3.0, this docking station provides data transfer rates of up to 5 Gbps, but is also backward compatible with USB 2.0 systems (data transfer rates up to 480 Mbps).

Features

- Dual SATA docking station enables the connection of two 2.5" or 3.5" hard drives via a computer's USB port.
- Easy set-up eliminates the need for time-consuming internal installation and facilitates access to a hard drive's contents.
- Offline cloning functionality allows hard drive duplication with the touch of a button – a host computer connection is not needed.
- An LED progress bar displays cloning status.
- Supports USB 3.0 connections with data transfer rates up to 5Gbps.
- Compliant with SATA HDD or SSD drives up to SATA III
- Backwards compatible with USB 2.0 and USB 1.1 standards.
- Docking functionality compatible with Windows, MAC, and Linux systems

Highlights

- Read and Write to two drives simultaneously
- Accepts 2.5" or 3.5" SATA drives up to 4TB
- Docking functionality compatible with Windows, MAC, and Linux systems

System Requirements

- (x2) 2.5" or 3.5" SATA Hard Drive.
- Computer with an available USB port. Note: A USB 3.0 port is required to achieve maximum transfer speeds up to 5Gbps. Cloning functionality does not require the U339-002 to be connected to a computer.
- Docking functionality compatible with Windows, Mac and Linux systems.
- Offline clone copies data from the master drive to the slave drive, leaving the remaining data unallocated. Windows computers will be able to reallocate the remaining data, whereas Mac and Linux computers will not.

Package Includes

- U339-002 USB 3.0 SuperSpeed to Dual SATA External Hard Drive Docking Station
- 4-ft. USB 3.0 Device Cable
- External Power Supply with NEMA 1-15P Plug (Input: 100-



240V, 50/60Hz, 1.2A;

Output: 12V, 4A)

- Owner's Manual

Specifications

MODEL TEXT	
Key Benefit	SuperSpeed (5Gbps) Data Transfer over USB 3.0
OVERVIEW	
AC Adapter	Input: 100-240V, 50/60Hz, 1.2A; Output: 12V, 4A
CONNECTIONS	
Side A - Connector 1	USB 3.0 A (MALE)
Side B - Connector 1	(2) 22 PIN SATA + POWER (FEMALE)
CERTIFICATIONS	
Certifications	CE, FCC, RoHS
WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>