

In most applications, a signal booster (Model Number: B121-000) should be used with this cable to ensure a signal strong enough for your display.

## DisplayPort Cable with Latches (M/M) 50-ft.

MODEL NUMBER: **P580-050**



### Description

DisplayPort is a new digital display interface standard put forth by the Video Electronics Standards Association (VESA). It defines a digital audio/video interconnect intended to be used between computer and display monitors, or computers and home theater systems. Similar to HDMI, in that it supports both Digital Video/Audio signals, DisplayPort is geared more toward the computer market, where HDMI dominates the Home Theater market. Tripp Lite's DisplayPort cables support a maximum bandwidth of 10.8Gbps, as well as DPCP ( DisplayPort Content Protection ) , HDCP, and resolutions up to 1080p. To achieve maximum performance, a signal booster such as the Tripp Lite [B121-000](#) must be used with this cable.

### Features

- The future standard for Digital Video and Audio connections
- Supports Displayport v1.2
- Provides up to 1080p resolution
- Monitor Resolution Support: 2560x1600 @ 60Hz, 1920x1200 @ 120Hz
- Supports High Definition Content Protection ( HDCP )
- To achieve maximum performance, a signal booster such as the Tripp Lite [B121-000](#) must be used with this cable

## Specifications

INPUT

### Highlights

- Digital Video and Audio in one cable
- Supports 1080p resolution
- Small footprint compared to VGA or DVI
- To achieve maximum performance, a signal booster such as the Tripp Lite [B121-000](#) must be used with this cable

### Package Includes

DisplayPort Monitor Cable - 50ft



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Cable Length (ft.)	50
Cable Length (m)	15.2
<b>PHYSICAL</b>	
Color	Black
<b>CONNECTIONS</b>	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DISPLAYPORT (MALE)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<https://www.tripplite.com/products/product-certification-agencies>